V DATE	BY	CHK	DESCRIPTION	ON	ECN	SCALE N/A DRAWING NO / CAD FILE LCC10-14BW-CUS
2 12/04	_	JHNU	REVISED WIRE SIZE		12305	Copper Lug - Two-Hole, Long Barrel with Window
						LCC10-14BW-L
						PANDUIT CORP. TINLEY PARK, ILLING
	1					T
	CE	ERTIFIED	D LISTED Wire Connector			
				05±.01		
Die Index on Barrel	No. ()]		.13±.01 .22±.01
on Barrel Alternate Industry			N/A		Wire inspect	ion window————————————————————————————————————
on Barrel Panduit Die Index No.						
Panduit Color Code			N/A	_		
C.S.A Certified Wire Connector			Yes			2.00±.00
UL Temperature Rating			90° C			2.06±.06
UL Listed Wire Connector			Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.25±.04	75±.02	2 .27±.02 DIA (2) PLS
Stud Size			1/4 in.	.42±.04) P =	
Wire Strip Length		1	9/16 in.		\	
Wire Type			Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric]		
Wire Size			14 - 10 AWG STR, 12 - 10 AWG SOL			.37 R Ref
Plating			Electro-Tin			
Material			High Conductivity Seamless Copper Tube			

Г