THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.								
Mate	ərial			High Conductivity Seamless Copper Tube]			
Platir	ng			Electro-Tin			.63 R Ref	
Wire	Wire Size			500 STR/FLEX]		Color coded	
Wire	Wire Type			Stranded Copper: Class G, H, I, K, M, Locomotive		//FLEX	barrel markings	
Wire	Wire Strip Length		١	1-9/16 in.		ナ do		
Stud	Stud Size			1/2 in.		50		
	UL Listed Wire Connector			Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.63±.07 —	- − 1.75:	5±.02	
	UL Temperature Rating			90°C			5.25±.09	
	C.S.A Certified Wire Connector			Yes			← 1.48±.07 → Beveled wire	
	Panduit Color Code on Barrel		ode	PINK		Wire inspection window		
	Panduit Die Index No. on Barrel		x No.	P99			1.03±.01 1.30±.01	
Die Ir	Alternate Industry Die Index No. () on Barrel		у	(L99)				
		CE	RTIFIE	 LISTED Wire Connector 	.26±.01 —			
							ANDUIT CORP. TINLEY PARK, ILLINOIS	
							LCDX500-12-6	
01 4			JHNU	REVISED TOLERANCES: HOLE OFFSET WAS .04, BARREL LENGTH WAS .04 OVERALL LENGTH WAS .06			Copper Lug - Two-Hole, Standard Flex Barrel	
REV D	ATE	BY	СНК	DESCRIPT	ION	ECN	SCALE DRAWING NO / CAD FILE N/A LCDX500-12-CUST	