


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	PACKG. QTY.	LENGTH "L" ±1.00" [25.4mm]
HTMLT38WEH-Q	25	124.75 [3169]

- NOTES:
1. MATERIAL: 304 STAINLESS STEEL
 2. BRACKETS [] DENOTES DIMENSIONS IN MILLIMETERS.
 3. INSTALLATION TOOLS: RT2HT, ST2MT & ST4MT



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04	11-05-15	JBN	SKB	RGRO	ADDED INSTALLATION TOOLS: RT2HT & ST4MT	13L040BE-DC
03	10-08-15	JBN	SKB	RGRO	REMOVED FROM DRAWING: HTMLT26WEH-Q, BUNDLE DIAMETERS & INSTALLATION TOOLS RT2HT, PBTMT	13L040BE-DC
02	06-11-15	BDK	SKB	RGRO	REMOVED FROM DRAWING: HTMLT12WEH-Q; HTMLT16WEH-Q; CUSTOMER/APPROVAL LINE	13L040BE-DC
01	04-04-14	ACC	AJN	RGRO	UPDATED PART LENGTHS	
00	03-31-14	JBN	ACC	RGRO	DRAWING RELEASED	

TITLE		HEAT TRACE WAVE TY (HTMLT38WEH-Q) CUSTOMER DRAWING	
ITEM REVISION NAME		13L040BE/03	
DATASET FILE NAME		13L040BE_DC/03A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ±		.XXX ± ANGLES ±	
THIRD ANGLE PROJECTION		SEE NOTES	
DRAWN BY JBN		DATE 03-31-14	
CHK ACC		SCALE N.T.S.	
DRAWING NUMBER: 13L040BE-DC		SHT 1 OF 1	
SIZE A			