THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. 17,4" 76mm 442,5mm 1,1" 29mm 0 Ю 0 13,2" 336,5mm PANDUIT VIBR <70dB <2,5m/s2 12.1 Ton =+40°C -4°F (108 kN) -20°C BiO CT-2920/CCPBT, 12 TON MULTI-USE (CRIMP-CUT-PUNCH) TOOL This tool meets requirements for Safety for Handheld

 B

Motor-Operated Electric Tools specification UL 60745-1 and CSA C22.2 No. 60745-1.

Tool is listed under CSA file number 80103907. Tool meets OSHA mandated electrical and mechanical product safety requirements.

1-11-22

11-24-21

DATE

REVI

BJPU JEH

BY CHK APR

JADE RELEASED FOR PRODUCTION

GENERAL NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.

2. DIMENSIONS IN [] ARE METRIC.
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF ROHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITEE.

TOOL SPECIFIC NOTES:

- 1. THE CT-2920/CCPBT BATTERY OPERATED MULTI-USE TOOLS ARE
- DESIGNED TO CRIMP, CUT AND PUNCH (WITH ACCESSORIES.)
 THE TOOL CRIMPS PANDUIT COPPER AND ALUMINUM COMPRESSION CONNECTORS USING PANDUIT CRIMPING DIES. GO TO www.panduit.com FOR MORE INFORMATION.

THE TOOL CUTS ALUMINUM AND COPPER CODE CONDUCTOR CABLE UP TO 1.57" [40mm].

- THE TOOL CUTS ALUMINUM AND MILD STEEL THREADED ROD; M5 TO MI2, AND 1/4 TO 1/2 UNC THREAD.
- PUNCH CAPACITY OF 5-5/8" [144 mm] CONDUIT SIZE IN 10 GAUGE [3.41 mm] MILD STEEL WITH STANDARD GREENLEE PUNCHES AND PANDUIT PUNCH DRIVE ADAPTER.
- THIS TOOL CAN OPERATE WITH BLUE TOOTH TECHNOLOGY TO CONNECT TO THE I-PRESS PHONE APP TO MONITOR CRIMP PERFORMANCE.

THE CT-2920/CCPBT TOOL KIT INCLUDES:

QTY. DESCRIPTION/ITEM

- BATTERY OPERATED 12 TON HYDRAULIC MULT-USE (CRIMP, CUT PUNCH) TOOL
- RECHARGEABLE BATTERIES (MAKITA LITHIUM-ION 18VDC, 4Ah)
- MAKITA BATTERY CHARGER 120VAC (WITH US PLUG CONFIGURATION)

PART NUMBER

TOOL CASE

SET OF "UA12TKL" DIE ADAPTERS

TECHNICAL INFORMATION:


- TOOL WEIGHT (INCLUDING BATTERY) 14.3 LBS. [6.5 kg]
- 2. DIMENSIONS (INCLUDING BATTERY) 17.4" L x 13.2" H x 3.0" W $[442.5 L \times 336.5 H \times 76 W] mm$

CRIMPING FORCE 12 TONS [108 KN]

- 4. TOOLS ARE TO BE USED WITH PANDUIT CRIMP DIES, CABLE CUTTERS, THREADED ROD CUTTERS AND PUNCH DRIVE ADAPTERS AND ARE SOLD SEPARATELY. (GO TO www.panduit.com FOR MORE INFORMATION.)

 5. A COPY OF OPERATION MANUAL AND ACCESSORY INFORMATION CAN
- BE FOUND AT: www.panduit.com.

DIMENSIONS IN [BRACKETS] ARE IN MILLIMETERS. ALL DIMENSIONS ARE FOR REFERENCE ONLY.



CT-2920/CCPBT