


B

Α

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



00

REV

11-24-21

DATE

BJPU

JEH

BY CHK APR

JADE RELEASED FOR PRODUCTION

DESCRIPTION

2

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT. 2. DIMENSIONS IN [] ARE METRIC. 3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITEE. THE CT-2940/STBT BATTERY OPERATED TOOLS ARE DESIGNED TO CRIMP WITH PANDUIT CRIMP DIES.
CRIMPS PANDUIT COPPER AND ALUMINUM COMPRESSION CONNECTORS USING PANDUIT CRIMPING DIES. GO TO www.panduit.com FOR MORE THIS TOOL CAN OPERATE WITH BLUE TOOTH TECHNOLOGY TO CONNECT TO THE i-PRESS PHONE APP TO MONITOR CRIMP PERFORMANCE.

THE CT-2940/STBT TOOL KIT INCLUDES: BATTERY OPERATED 15 TON HYDRAULIC CRIMP TOOL RECHARGEABLE BATTERIES (MAKITA LI-ION 18VDC, 4Ah) MAKITA BATTERY CHARGER - 120VAC (WITH US PLUG CONFIGURATION) HANDLE (SCREW-IN)

В

Δ

1. TOOL WEIGHT (INCLUDING BATTERY) 17.6 LBS. [8.0 kg] 2. DIMENSIONS (INCLUDING BATTERY) 19.5" L × 13" H × 3.1" W [495.5 L × 331.3 H × 78 W] mm 3. CRIMPING FORCE 15 TONS [135 kN] 4. A COPY OF OPERATION MANUAL AND ACCESSORY INFORMATION CAN BE FOUND AT: www.panduit.com.

DIMENSIONS IN [BRACKETS] ARE IN MILLIMETERS. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

PART NUMBER

093806

ECN

CT-2940/STBT

CT-2940/STBT, Customer Drawing, 15 Ton, Next Generation Crimp Tool

CUSTOMER DRAWING					
EM REVIS	SION NAME				
	008288	ECA/02	×		
TASET FILE NAME					
00828ECA_DC/02				PANDU	
E			IRD ANGLE OJECTION		
TERIAL				DRAWING NUMBER	
AS NOTED				00828ECA_DC	
AWN BY	DATE	СНК	SCALE		SIZE
BJPU	11-24-21	JEH	NONE	SHEET 1 OF 1	В
1					