
Т	HIS COPY IS PROVIDED ON A	A RESTRICTED BASIS AND IS NOT TO BE U	SED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.
	Material	High Conductivity Seamless Copper Tube	
	Plating	Electro-Tin	.63
	Wire Size	750 STR/FLEX	
	Wire Type	Stranded Copper: Locomotive	PANDUIT (**) **So STR/FLEX (**) **CDXN750-12** **CDXN750-12
	Wire Strip Length	1-3/4 in.	1.50±.04
	Stud Size	1/2 in.	
	UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.63±.07 1.75±.02 5.55±.09 .53±.0
	UL Temperature Rating	90° C	
	C.S.A Certified Wire Connector	Yes	
	Panduit Color Code on Barrel	YELLOW	Wire inspection window—
	Panduit Die Index No. on Barrel	P115	
	Alternate Industry Die Index No. () on Barrel	(L115)	







							CORP. TINI	LEY PARK, ILLINOIS
05	4/09	JHNU	JHNU	REVISED OVERALL LENGTH: WAS 4.60 REVISED TONGUE THICKNESS: WAS .34		LCDXN750-12-3 Copper Lug - Narrow Tongue, Two-Hole, Standard Flex Barrel		
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A	DRAWING NO / CAD FILE	LCDXN750-12-CUST