THIS COPY IS	PROVID	ED ON	A RESTRICTED BASIS AND IS NOT TO BE US	ED IN ANY	WAY DETRIMENTA	L TO TI		ERESTS OF PANDUIT CORP.	
Material			High Conductivity Seamless Copper Tube						
Plating			Electro-Tin						
Wire Size			6 AWG		.37 R Ref				
Wire Type			Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	-					
Wire Strip Length		۱	7/8 in.	 .48±.0	04				
Stud Size	Stud Size		1/4 in.			ΓA β			
UL Listed Wire Connector			Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.25	.25±.04 .63±.02 .27±.02 DIA (2) PLS				
UL Temperature Rating			90°C						
C.S.A Certified Wire Connector			Yes						
Panduit Color Code on Barrel		ode	BLUE						
Panduit Die Index No. on Barrel			P24						
Alternate Industry Die Index No. ( ) on Barrel			(7)		Wire inspect	ion wi	ndow-	.81±.04 — Beveled wire entry	
	CE	ERTIFIED	<ul> <li>LISTED Wire Connector</li> </ul>	.08±.01		1		.22±.01 .31±.01	
								CORP. TINLEY PARK, ILLINOIS	
02 6/19 JHNU JHNU		JHNU	moved panduit & ul/csa logos on stamp		N10884RY- LCD6-14A-CUST	RGB	RGB	LCD6-14A-L	
01 11/03 DRL DRL		DRL	REMOVED NAVY NUMBER FROM STAMP, MOVED PANDUIT, UL & CSA		11322			Copper Lug - Two-Hole, Standard Barrel	
REV DATE	BY	СНК	DESCRIPTION		ECN	-R	SUP	SCALE N/A DRAWING NO / CAD FILE LCD6-14A-CUST	