


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		
Wire Size	4/0 AWG		
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		
Wire Strip Length	1-5/8 in.		
Stud Size	1/2 in.		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90° C		
C.S.A Certified Wire Connector	Yes		
Panduit Color Code on Barrel	PURPLE		
Panduit Die Index No. on Barrel	P54		
Alternate Industry Die Index No. () on Barrel	(15)		











LISTED
Wire Connector

						CORP. TINLEY PARK, ILLINOIS
						LCB4/0-12WF-X Copper Lug - One-Hole, Long Barrel with Window, 90° Angle Tongue
00	4/17	JHNU	JHNU	DRAWING RELEASED	021775	Copper Log - Offe-flore, Long Bullet Will William, 70 Angle Tongoe
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCB4/0-12WF-CUST