тніѕ с	OPY IS F	ROVID	ED ON	A RESTRICTED BASIS AND IS NOT TO BE	USED IN ANY WAY DETR	IMENTAL TO THE INT	ERESTS OF PANDUIT CORP.	
Ма	Material			High Conductivity Seamless Copper Tube				
Plat	Plating			Electro-Tin		4 Window		
Wire	Wire Size			750 kcmil	1.89±.04	PANDUIT BP750-12W CB750-12W		
Wire	Wire Type			Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric				
Wire	Wire Strip Length		I	2-15/16 in.	.63±.07	.53±.02 DIA		
Stu	Stud Size			1/2 in.		<b>-</b> 1.38±.04 <b>-</b>		
	UL Listed Wire Connector			Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.				
	UL Temperature Rating			90° C	.26±.01 —	90°±5°	4.18 REF 2.88±.07 BLACK DIE P106 (24)	
	C.S.A Certified Wire Connector			Yes				
	Panduit Color Code on Barrel		ode	BLACK				
	Panduit Die Index No. on Barrel		ex No.	P106				
Die	Alternate Industry Die Index No. ( ) on Barrel			(24)				
		CE	RTIFIEL	B LISTED Wire Connector	_	1.03±.01 — 1.30±.01 — 2.92	Beveled wire entry REF	
							1	
							CORP. TINLEY PARK, ILLINOIS	
01	)1 3/18 JHNU JHNU		JHNU	REVISED O.D.: 1.30 WAS 1.19 REVISED I.D.: 1.03 WAS .92		00094EEE- LCB750-12WF-CUST	LCB750-12WF-6 Copper Lug - One-Hole, Long Barrel with Window, 90° Angle Tongue	
00	) 4/17 JHNU JHNU		JHNU	DRAWING RELEASED		021775		
EV	DATE	BY	СНК	DESCRIP	TION	ECN	SCALE N/A DRAWING NO / CAD FILE LCB750-12WF-CUST	