



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	WEIGHT
FZBA1.5X4	0.29 LB/EACH 132g/EACH

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
- THE FIBER ROUTING ADJUSTABLE "Z" BRACKET ALLOWS FOR FIBER-DUCT 2x2 OR 4x4, FIBERRUNNER 2x2 AND/OR PANDUCT TYPES H AND HS 4x4 HINGED WIRING DUCT TO BE ATTACHED VERTICALLY TO THE FRONT OR REAR OF TELCO OR TIA/EIA RACKS.
- THE FIBER ROUTING ADJUSTABLE "Z" BRACKET KIT INCLUDES:
 ONE (1) BRACKET (RACK SIDE),
 ONE (1) BRACKET (DUCT SIDE),
 TWO (2) #10-32x1/2 PHILLIPS TRUSS-HEAD MACHINE SCREWS,
 TWO (2) #10 HELICAL SPRING LOCKWASHERS,
 TWO (2) #10-32 MACHINE SCREW NUTS,
 ONE (1) BAG OF FOUR (4) #12-24x1/2 TYPE 1 COMBINATION DRIVE ROUND HEAD MACHINE SCREW, DOG POINTED
- FINISH COLOR: BLACK (EXCEPT FOR HARDWARE)
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38566BG_DC_FZBA1.5X4_01.prt

CAD FILENAME/LAYERS: **FZBA1.5X4.pdf**

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
2	8-2-06	MSO	RN	I. REVISED PART WEIGHT. H. REVISED GENERAL NOTES.	38566-07	RN	RN		
-	-----	---	--	G. REVISED CAD FILENAME.	-----	--	--		
-	-----	---	--	F. REVISED MATERIAL REF. E. RELOCATED DIMENSIONS.	-----	--	--		
-	-----	---	--	D. ADDED DIMENSIONS. C. REMOVED DIMENSIONS.	-----	--	--		
1	8-30-04	MSO	RN	B. REVISED GENERAL NOTES. A. REVISED DRAWING TITLE.	38566-07	RN	RN		
R	4-28-03	MSO	RPA	RELEASED TO PRODUCTION	38566-07	RN	RN		

PANDUIT CORP TINLEY PARK, ILLINOIS

FIBER ROUTING ADJUSTABLE "Z" BRACKET (FZBA1.5X4)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ±
 (.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: MSO
 DATE: 4-28-03
 CHECK'D: RPA

MAT'L: STEEL

SCALE: NONE

DRAWING NO.: 38566-07
 DWG SIZE: A