
Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		C U S F
Wire Size	750 kcmil		SIR C 588GF
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	1.89±.04	PANDUIT COULT COUL
Wire Strip Length	1-15/16 in.		
Stud Size	5/8 in.	.63±.04 —	1.50±.02 →
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		2.81±.04
UL Temperature Rating	90° C	.2 <u>6±.01</u>	
C.S.A Certified Wire Connector	N/A		
Panduit Color Code on Barrel	BLACK	1	90°±5°
Panduit Die Index No. on Barrel	P106		
Alternate Industry Die Index No. () on Barrel	(24)		





						CORP. TINLEY PARK, ILLINOIS	
					000 (70	LCD750-58GF-6 Copper Lug - Two-Hole, Standard Barrel, 90° Angle Tongue	
00	6/17	JHNU	JHNU	DRAWING RELEASED	022679		
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCD750-58GF-CUST	