



2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

# NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. REFERENCE TIA-568-C.O. FOR DETAILS ON METHOD A CONNECTIVITY.
4. MATERIALS:  
A. FRONT PANEL: STEEL  
B. BOX AND LID: ALUMINUM  
C. ADAPTERS: COMPOSITE PLASTIC
5. CASSETTE WEIGHT: 39.0oz (1100.0g)
6. DIMENSIONS IN BRACKETS ARE METRIC
7. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



ISOMETRIC VIEW


							TITLE				
							HDQ SERIES FIBER OPTIC ANGLED CASSETTES FOR BROCADE 32 PORTS (64 FIBERS)				
							CUSTOMER DRAWING				
							ITEM REVISION NAME 12F193AC/01			<div>PANDUIT</div>	
							DATASET FILE NAME 12F193AC_DC/01A				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ] <div>.X ± .XXX ± .010 [ 0.3 ] .XX ± .03 [ 0.8 ]      ANGLES ±</div>				
							<div></div> THIRD ANGLE PROJECTION				
R	05-15-13	SAT	YMG		RELEASED TO PRODUCTION	12F193AC-DC	DRAWING NUMBER: 12F193AC-DC				
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 05-15-13	CHK YMG	SCALE NONE	SIZE A
							SHT 1 OF 3				

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TABLE 1 - HDQ SERIES FIBER OPTIC CASSETTE - MPO TO LC 10 GbE 1RU ANGLED PROFILE; 64-FIBER BROCADE LABELING	
PART NUMBER	DESCRIPTION
METHOD A	
F1ABXN-6408-10S	OM3 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ABXO-6408-10S	OPTIMIZED OM3 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ABZN-6408-10S	OM4 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ABZO-6408-10S	OPTIMIZED OM4 FIBER; 8-FIBER MPO TO DUPLEX LC
MODIFIED METHOD A, PAIR FLIPPED	
F1ABXN-6408-10F	OM3 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ABXO-6408-10F	OPTIMIZED OM3 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ABZN-6408-10F	OM4 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ABZO-6408-10F	OPTIMIZED OM4 FIBER; 8-FIBER MPO TO DUPLEX LC

						TITLE	HDQ SERIES FIBER OPTIC ANGLED CASSETTES FOR BROCADE 32 PORTS (64 FIBERS)					
						ITEM REVISION NAME	CUSTOMER DRAWING					
						DATASET FILE NAME	12F193AC_01					
							12F193AC_DC/01A					
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ] .X ± .XXX ± .010 [ 0.3 ] .XX ± .03 [ 0.8 ] ANGLES ±						
						 THIRD ANGLE PROJECTION						
R	05-15-13	SAT	YMG		RELEASED TO PRODUCTION	12F193AC-DC	MATERIAL:  SEE NOTES SHEET 1					
							DRAWING NUMBER: 12F193AC-DC					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE	
							SAT	05-15-13	YMG	NONE	A	

