

## **NOTES, UNLESS OTHERWISE SPECIFIED:**

**PANDUIT CT-1551 TOOL:** 

**TOOL WEIGHT: 27.2 oz. [77] kg** 

Crimps most Panduit #22-#10 AWG insulated terminals & splices, and specific insulated disconnects.

Reduced crimp effort advantage for #12-#10 AWG terminations.

Provides UL Listed and CSA Certified terminations with applicable Panduit terminals.

DIMENSIONS SHOWN IN BRACKETS [] ARE METRIC, AND ARE FOR REFERENCE ONLY.

	ENG	LISH	METRIC		
CRIMP	GO / NO	GO GAGE	GO / NO GO GAGE		
POCKET	MEM	BERS	MEMBERS		
AWG / mm <sup>2</sup>	"G" Dia.	"NG" Dia.	"G" Dia.	"NG" Dia.	
	(GO)	(NO GO)	(GO)	(NO GO)	
22-14/0,5-2,5	0.096"	0.106"	2,43 mm	2,69 mm	
12-10/4,0-6,0	0.147"	0.155"	3,73 mm	3,93 mm	

							CT-1551 Contour Crimp™ Crimping Tool CUSTOMER DRAWING		
							TD27602P04 04	MDUIT	
					UPDATED THE LOGO ON THE TOOL		TP27603B01_01  UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		
01	2-10-17	BLR	ВЈРИ	JADE	FRAME, ADDED GO – NO GO CHART.  REMOVED PANDUIT LOGO AND MADE IN GERMANY FROM THE GRIPS;	4857/ 02	(.x) ± (.xxx) ± (.xxx) ±		
00	5-11-15	BLR	BJPU	ABJ	RELEASED	4857	1 +	G NUMBER: P27603B01	
REV	DATE	ВҮ	СНК	APR	DESCRIPTION	ECN	BLR 5-11-15 BJPU NONE SH	HT 1 OF 1 B	