

## THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.






#10 MECHANICAL CLAMP, 9/16" - 1-1/16" DIAMETER RANGE #16 MECHANICAL CLAMP, 15/16" - 1-1/2" DIAMETER RANGE



BLACK POLYPROPYLENE COVER; CVR250 BLACK POLYPROPYLENE COVER; CVR500



#12-24 SLOTTED HEX-HEAD ZINC PLATED THREAD-FORMING SCREW

M6 SLOTTED HEX-HEAD ZINC PLATED THREAD-FORMING SCREW

## NOTES:

- 1. KIT INCLUDES JUMPER WIRE ASSEMBLY, MECHANICAL CLAMP, THREAD-FORMING SCREWS, AND TERMINAL COVER.
- 2. FOR USE WITH UNJACKETED ARMOR CABLE. DIAMETER RANGE .440" 1.250".
- 3. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS

COMPONENT	ACG24K	ACG24K-500	ACG24KX-500
DESCRIPTION	COMPONENT QTY.	COMPONENT QTY.	COMPONENT QTY.
24" JUMPER ASSEMBLY	1	1	1
#10 MECHANICAL CLAMP	1	1	N/A
#16 MECHANICAL CLAMP	N/A	N/A	1
BLACK POLYPROPYLENE COVER - CVR250	1	N/A	N/A
BLACK POLYPROPYLENE COVER - CVR500	N/A	1	1
#12-24 THREAD FORMING SCREW	2	2	2
M6 THREAD FORMING SCREW	2	2	2

							ARMORED CABLE GROUNDING JUMPER KIT	
06	8/21	JHNU	JHNU	JADE	REMOVED 16mm FROM WIRE DESCRIPTION	104433	ITEM REVISION NAME	
05	7/11	JHNU	JHNU	FLD	REVISED TABLE TO REMOVE PART ALREADY IN TABLE	N41753BB-C41753		
04	5/11	JHNU	RWK	FLD	REVISED NOTE 2: 1.250" WAS 1.000"	N41753BB-C41753	DATASET FILE NAME	
03	5/11	JHNU	RWK	FLD	REMOVED ACG24KX FROM DRAWING	N41753BB-C41753	C41753_06.SLDDRW	
02	4/11	JHNU	RWK	FLD	ADDED PART NUMBER ACG24KX-500, ACG24KX	N41753BB-C41753	UNLESS OTHERWISE SPECIFIED,  DIMENSIONAL TOLERANCES ARE: IN [mm]	
01	9/08	JHNU	JMAR	JAC	ADDED P/N ACG24K-500 ADDED TABLE TO CLARIFY COMPONENT QUANTITIES		.X ± .XXX ± SEE NOTES  .XX ± ANGLES ±	
00	6/08	JHNU	JMAR	JAC	DRAWING RELEASED		THIRD ANGLE PROJECTION C41753_06	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE  JHNU 6/08 JMAR NONE SHEET 1 OF 1 B	