

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





TABLE - 1		
ASSEMBLY PART NUMBER	ITEM DESCRIPTION	WEIGHT
FSCBT3BU-X	OPTICAM 3.0mm CABLE RETENTION BOOT ASSEMBLY WITH BLUE BOOT	3.53g/10 Pcs [.125oz/10 Pcs]
FMCBT3AQ-X	OPTICAM 3.0mm CABLE RETENTION BOOT ASSEMBLY WITH AQUA BOOT	
FMCBT3BL-X	OPTICAM 3.0mm CABLE RETENTION BOOT ASSEMBLY WITH BLACK BOOT	
FMCBT3EI-X	OPTICAM 3.0mm CABLE RETENTION BOOT ASSEMBLY WITH ELECTRIC IVORY BOOT	



NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR ADDITIONAL INFORMATION PERTAINING TO THESE PRODUCTS.
- 10 ASSEMBLIES PER PACKAGE.
- MATERIALS:
A. RETENTION NUT: PLASTIC
B. BOOT: RUBBER
- PRIMARY DIMENSIONS ARE METRIC, DIMENSIONS IN BRACKETS ARE CUSTOMARY.

						TITLE OPTICAM 3.0mm CABLE RETENTION BOOT ASSEMBLY CUSTOMER DRAWING	
						ITEM REVISION NAME M01799AY/03	
						DATASET FILE NAME M01799AY_DC_3MMX/03A	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .xxx ± .010 (0.3) .xx ± .03 (0.8) ANGLES ±	
						PART NO. SEE TABLE 1	
						DRAWING NUMBER: 01799-46	
02	06-09-14	SAT	WJM	RWB	RELEASED TO PRODUCTION	01799-46	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	
						DRAWN BY MC	DATE 07-31-06
						CHK JAW	SCALE NONE
						SHT 1 OF 1	
						SIZE A	