



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DETAIL B
CABLE LENGTH



PART NUMBER	LENGTH +6" (152.4) / -2" (50.8)	WEIGHT
UTPCH8SR25Y	8' (2438.4)	1.20 LB/EACH (545 G/EACH)
UTPCH10SR25Y	10' (3048)	1.44 LB/EACH (654 G/EACH)
UTPCH15SR25Y	15' (4572)	2.05 LB/EACH (932 G/EACH)
UTPCH20SR25Y	20' (6096)	2.66 LB/EACH (1209 G/EACH)
UTPCH6SR25Y	6' (1829)	.96 LB/EACH (435 G/EACH)

NOTES:

1. SEE CURRENT CATALOG TO INDICATE PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. MATES WITH FEMALE RJ21 CONNECTOR AND 10/100 BASE T PATCH PANEL.
4. CATEGORY 5 AND POWER SUM RATED.
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.

PART NUMBER		UTPCH**SR25Y	
TITLE		25 PAIR PATCH CORD ASSEMBLY ONE 110° RIGHT RJ21 MALE CONNECTOR AND ONE 180° RJ21 CONNECTOR	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		M02479KI_00	
MATERIAL:		CONNECTOR HSG: UL94 V-0 THERMOPLASTIC CABLE JACKET: PVC	
DRAWING NUMBER:		02479-270	
DRAWN BY		NER	
DATE		3-20-06	
CHK		NONE	
SCALE		SHT 1 OF 1	
SIZE		A	