




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	WEIGHT
PZAEWM3	63.2 LB/EACH PC (28.7 Kg/EACH PC)

NOTES:

- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- PART INCLUDES:
 - 1- ENCLOSURE BASE
 - 1- ENCLOSURE DOOR
 - 36"- EDGE GROMMET
 - 10- TAK-TY'S™
 - 4- BEND RADIUS CLIP
 - 1- GROUNDING STRAP
 - 1- GROUNDING HARDWARE
 - 2- PORT ID LABEL
 - 1- DOOR LATCH AND HARDWARE
 - 2- SET OF HINGES AND HARDWARE
 - 1- WALL TEMPLATE

SEE SHEET #2 FOR MATERIAL DETAILS



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
07B	1-29-19	RYB			A. ADDED DIMENSION FROM EQUIPMENT MOUNT SURFACE TO THE ENCLOSURE FLOOR FOR REFERENCE	M01247A0
07A	12-22-16	TWV	BAME	KRKE	ADDED MAX EQUIPMENT DEPTH TO SHEET 2	01247-41
R	10/02/03	JSP			DRAWING RELEASED	01247-41

TITLE				PANZONE™ ACTIVE WALL MOUNT ENCLOSURE CUSTOMER DRAWING			
				CONTROL DRAWING			
ITEM REVISION NAME				M01247A0/07			
DATASET FILE NAME				M01247A0_DC/07B			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:				MATERIAL:			
				STEEL			
				DRAWING NUMBER:			
				01247-41			
DRAWN BY		DATE		CHK		SCALE	
JSP		10/2/03				NONE	
THIRD ANGLE PROJECTION				SHT 1 OF 2			
				A			

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

KNOCKOUT FOR T70 RACEWAY (4 PLCS.)

KNOCKOUT FOR 1/2" OR 3/4" CONDUIT. (4 PLCS.)

LOUVERED VENTS

KNOCKOUT FOR 1-3/4" OR 2" CONDUIT. (10 PLCS.)

24.00 [609.6]

PATCH PANEL BRACKET ROTATES 90° TO ALLOW ACCESS TO REAR OF PATCH PANELS.

3 RACK UNITS FOR PATCH PANELS.

PATCH PANEL BRACKET SHOWN IN THE DOWN POSITION.

3 RACK UNITS FOR ACTIVE EQUIPMENT WITH 21" MAX EQUIPMENT DEPTH.

SPACE AVAILABLE FOR A DOUBLE GANG ELECTRICAL BOX. (2 PLCS)

GROUNDING STUDS LOCATED ON BOTH THE DOOR AND ENCLOSURE BASE.

VENTING FOR A 4.68" FAN. (2 PLCS)

VIEW SHOWN WITH DOOR REMOVED.

16.00 [406.4]

25.50 [647.7]

21.25 [539.8]

OPEN SPACE FROM EQUIPMENT MOUNT TO ENCLOSURE FLOOR

REAR WALL

CONNECTION AREA CONSISTS OF:
 REAR WALL - #16 GA CRS
 ASTM A653 CS TYPE B
 MOUNTING HARDWARE PROVIDED BY CUSTOMER

TITLE		PANZONE ACTIVE WALL MOUNT ENCLOSURE CUSTOMER DRAWING	
		CONTROL DRAWING	
ITEM REVISION NAME		M01247A0/07	
DATASET FILE NAME		M01247A0_DC/07B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL:	
		STEEL	
		DRAWING NUMBER:	
		01247-41	
DRAWN BY		DATE	CHK
JSP	10/2/03		
THIRD ANGLE PROJECTION		SCALE	
SHT 1 OF 1		SIZE	A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
07B	1-29-19	RYB			SEE SHEET ONE FOR REVISIONS	01247-41
R	10/2/03				DRAWING RELEASED	01247-41