


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



SPECIFICATION:


- STANDARD
 UNIT TYPE: BASIC
 ORIENTATION: VERTICAL, 0U MID
 OUTLET QTY & TYPE: (24)C13, (6)C19
 INPUT VOLTAGE: 100-240VAC
 INPUT FREQUENCY: 50/60HZ
 INPUT CURRENT: 32A
 BREAKER QTY & TYPE: (2)16AMP, SINGLE-POLE
 INPUT PHASE: SINGLE-PHASE
 RATED POWER: 7.4 kVA
 INPUT PLUG: IEC 60309 2P+E 6H 32A
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
 REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL:
 NONE
- ACCESSORIES:
 DOCUMENTATION KIT
 PRODUCT SAFETY WARNING SHEET

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION:

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E30B06M-XXYZ




PLUG / RECEPTACLE BLOCK



PLUG
 IEC 60309 2P+E 6H
 IP44 (SPASHPROOF)
 32A, 250VAC MAX RATED INPUT



RECEPTACLE
 IEC 60320 C13
 10A, 250V MAX RATED OUTPUT




RECEPTACLE
 IEC 60320 C19
 16A, 250V MAX RATED OUTPUT

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E30B06M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU E30B06M CONTROL DRAWING		
ITEM REVISION NAME:		PANDUIT
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL / COLOR: N/A
Tolerance (mm) 0 < L ≤ 50 ± 0.5 50 < L ≤ 250 ± 1.0 250 < L ≤ 500 ± 1.5 500 < L ≤ 1000 ± 2.5 1000 < L ≤ 2000 ± 4.0		DRAWING NUMBER: E30B06M_DC
THIRD ANGLE PROJECTION	DRAWN BY: LL	DATE: 08/29/2023
	CHK: MIM	SCALE: NONE
		SHT 1 OF 2
		SCALE: B

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E30B06M	BASIC PDU, 32A, (24)C13 (6)C19, IEC 60309 2P+E 6h IP44-3M, TOP-FED, BLACK	BLACK(RAL 9005)	3M(+254MM/-127MM)[10'(+10"/-5"']	6.3kg

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU E30B06M CONTROL DRAWING		
ITEM REVISION NAME:		PANDUIT
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
 Tolerance (mm) 0 < L ≤ 50 ± 0.5 50 < L ≤ 250 ± 1.0 250 < L ≤ 500 ± 1.5 500 < L ≤ 1000 ± 2.5 1000 < L ≤ 2000 ± 4.0 THIRD ANGLE PROJECTION		DRAWING NUMBER: E30B06M_DC
DRAWN BY	DATE	SCALE
LL	08/29/2023	NONE
CHK	MIM	SHT 2 OF 2
		SCALE B

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E30B06M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN