THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. 1. CABLE ASSEMBLY (WITH CONNECTORS): A. SEE SHEET 2 FOR PART NUMBER MATRIX. B. CANNOT BE LESS THAN THE LENGTH SPECIFIED IN THE PART NUMBER.
C. THE MAXIMUM CABLE LENGTH IS NOT TO EXCEED 10cm (4") OVER
SPECIFIED LENGTH FOR LESS THAN 10 METER; AND +1%/-0% GREATER FIBER OPTIC CONNECTOR TYPES THAN 10 METERS.
TIP TO TIP LENGTH IS MEASURED WITHOUT DUST CAPS INSTALLED.
PATCHCORD ROUTING CONFIGURATION IS "A" TO "B".
THIS DRAWING SHALL BE APPLICABLE TO ANY LENGTH PATCHCORD AS (POSITIONS 9 AND 11 OF PART NUMBER) DESIGNATED BY THE PART NUMBER, WHERE MEMETER. A. OPERATING TEMPERATURE RANGE IS FROM -10 C TO +60 C.
B. CONNECTORS ARE 'FOCIS' COMPLIANT.
C. CABLE ASSEMBLIES COMPLY WITH THE REQUIREMENTS OF TIA/EIA-568-C.3 OR EQUIVALENT IEC STANDARDS.

D. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL PUSH PULL DUPLEX LC DUPLEX LC DUPLEX SC RESTRICTIONS OF ROHS, (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS (TYPE Q) (TYPE L) (TYPE S) TECHNICAL ADAPTATION COMMITTEE. 3. PACKAGING:
A. CABLE ASSEMBLY SHIPPED WITH DUST CAPS INSTALLED.
B. UNIT QUANTITY: I PATCHCORD/PIGTAIL PER BAG.
4. PAIR FLIPPED PATCH CORDS SHALL HAVE A GREEN COLORED CABLE LABEL ON B EACH END WITH "PAIR FLIPPED" ON EACH LABEL. CONNECTOR INSERTION/RETURN LOSS SPECIFICATIONS MINIMUM RETURN LOSS MAXIMUM INSERTION LOSS (PER CONNECTOR) (PER CONNECTOR) CONNECTOR STANDARD OPTIMIZED ULTRA-LOW SM (UPC) SM (UPC) MM (PC) MM (PC) MM (PC) DUPLEX LC 0.35dB 0.25dB 0.15dB 55dB 26dB 0.10dB 0.50dB 26dB DUPLEX SC 0.25dB 0.15dB 55dB 0.10dB PUSH-PULL LC 0.35dB 0.15dB 55dB 26dB 0.25dB 0.10dB A CORDS CUSTOMER DRAWING TEM REVISION NAME M02779DX/00 DATASET FILE NAME

JACKETED DUPLEX FIBER PATCH M02779DX_DC/00C C. ADDED "PAIR FLIPPED" CABLE LABEL TO PAIR FLIPPED PATCH CORDS. UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] 02 11/17/16 **JSP** $M \cup W$ RWB M02779DX-DC B. ADDED (T)STD IL PAIR FLIPPED & (P)OPT IL PAIR FLIPPED. .x ± .03 [.762] M02779DX-DC 01 07-06-16 RWD MMN SAT ADDED (R)RISER AND (L)LSZH TO 5th POSITION. .xx ± .01 [.25] ANGLES ± 1 ° RAWING NUMBER: 00 01-06-16 SAT RWB RWB RELEASED TO PRODUCTION M02779DX-D0 M02779DX-DC PROJECTION CHK APR DESCRIPTION REV DATE ΒY SAT | 01-04-16 | RWB NONE SHT 1 OF 2

