



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

MPO KEY ON LEFT



NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:
 - A. MODULE MATERIAL: PLASTIC
 - B. ADAPTER: COMPOSITE PLASTIC
4. FIBER ROUTING: SEE SHEET 2.
PART NUMBERS: SEE SHEET 3.
5. CASSETTE MODULE WEIGHT: 2.4oz [69.0g]
6. DIMENSIONS IN BRACKETS ARE METRIC
7. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.




VIEW SHOWN WITH
DUSTCAPS

LC ADAPTER KEYS ORIENTED DOWNWARD

TITLE		QUICKNET SFQ SERIES CASSETTE, 4-1 DUPLEX LC TO MPO BREAKOUT CASSETTE	
CUSTOMER DRAWING		PANDUIT	
ITEM REVISION NAME	13F244AK/02		
DATASET FILE NAME	13F244AK_DC/02A	MATERIAL:	
ALL DIMENSIONS ARE FOR REFERENCE		SEE NOTE 3	
DRAWING NUMBER:		13F244AK-DC	
DRAWN BY	DATE	CHK	SCALE
BSN	07-26-16	WJM	1:2
THIRD ANGLE PROJECTION		SHT 1 OF 3	
REV		SIZE	
A		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	10-03-23	SAT	WJM	EJH	A. ADDED METHOD U AND U2 P/N's.	13F244AK-DC
00	07-26-16	BSN	EJH	SKE	RELEASED TO PRODUCTION	13F244AK-DC

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



LC PORT NUMBER 1 2 3 4

CONNECTORS KEY DOWN

4-1 BREAKOUT CASSETTE FIBER ROUTING									
METHOD A 8 FIBER CASSETTE (A)									
LC PORT NUMBER	1		2		X	3		4	
	A	B	A	B		A	B	A	B
MPO* FIBER POSITION	1	12	2	11		3	10	4	9
METHOD B 8 FIBER CASSETTE (B)									
LC PORT NUMBER	1		2		X	3		4	
	A	B	A	B		A	B	A	B
MPO** FIBER POSITION	1	12	2	11		3	10	4	9
METHOD U 8 FIBER CASSETTE (U)									
LC PORT NUMBER	1		2		X	3		4	
	A	B	A	B		A	B	A	B
MPO* FIBER POSITION	12	1	11	2		10	3	9	4
METHOD U2 8 FIBER CASSETTE (U2)									
LC PORT NUMBER	1		2		X	3		4	
	A	B	A	B		A	B	A	B
MPO* FIBER POSITION	1	12	2	11		3	10	4	9

(*) KEY UP/ KEY DOWN ADAPTER (BLACK ADAPTER).
 (**) KEY UP/ KEY UP ADAPTER (GRAY ADAPTER).

TITLE				QUICKNET SFQ SERIES CASSETTE, 4-1 DUPLX LC TO MPO BREAKOUT CASSETTE			
CUSTOMER DRAWING							
ITEM REVISION NAME				13F244AK/02			
DATASET FILE NAME				13F244AK_DC/02A			
ALL DIMENSIONS ARE FOR REFERENCE				PART NO. SEE TABLE			
DRAWING NUMBER: 13F244AK-DC				DRAWING NUMBER: 13F244AK-DC			
DRAWN BY BSN		DATE 07-26-16		CHK EJH		SCALE 1:2	
REV		DATE		BY		CHK	
APR		DESCRIPTION		ECN		SHT 2 OF 3	
						A	

SEE PAGE 1 FOR REVISION HISTORY							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



QUICKNET SFQ 8 FIBER LC CONVERSION CASSETTE - METHOD B	
FQ3XN-08-10B	8 FIBER / OM3 STANDARD LOSS
FQ3XO-08-10B	8 FIBER / OM3 OPTIMIZED LOSS
FQ3ZN-08-10B	8 FIBER / OM4 STANDARD LOSS
FQ3ZO-08-10B	8 FIBER / OM4 OPTIMIZED LOSS

QUICKNET SFQ 8 FIBER LC CONVERSION CASSETTE - METHOD A	
FQ3XN-08-10A	8 FIBER / OM3 STANDARD LOSS
FQ3XO-08-10A	8 FIBER / OM3 OPTIMIZED LOSS
FQ3ZN-08-10A	8 FIBER / OM4 STANDARD LOSS
FQ3ZO-08-10A	8 FIBER / OM4 OPTIMIZED LOSS
FQ39N-08-10A	8 FIBER / OS2 STANDARD LOSS

QUICKNET SFQ 8 FIBER LC CONVERSION CASSETTE - METHOD U	
FQ3ZO-08-10U	8 FIBER / OM4 OPTIMIZED LOSS
FQ3ZA-08-10U	8 FIBER / OM4 ULTRA LOW LOSS
FQ3SA-08-10U	8 FIBER / OM4+ ULTRA LOW LOSS
FQ3WO-08-10U	8 FIBER / OM5 OPTIMIZED LOSS
FQ3WA-08-10U	8 FIBER / OM5 ULTRA LOW LOSS
FQ39N-08-10U	8 FIBER / OS2 STANDARD LOSS
FQ39O-08-10U	8 FIBER / OS2 OPTIMIZED LOSS

QUICKNET SFQ 8 FIBER LC CONVERSION CASSETTE - METHOD U2	
FQ3ZO-08-10U2	8 FIBER / OM4 OPTIMIZED LOSS
FQ3ZA-08-10U2	8 FIBER / OM4 ULTRA LOW LOSS
FQ3SA-08-10U2	8 FIBER / OM4+ ULTRA LOW LOSS
FQ3WO-08-10U2	8 FIBER / OM5 OPTIMIZED LOSS
FQ3WA-08-10U2	8 FIBER / OM5 ULTRA LOW LOSS
FQ39N-08-10U2	8 FIBER / OS2 STANDARD LOSS
FQ39O-08-10U2	8 FIBER / OS2 OPTIMIZED LOSS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
					SEE PAGE 1 FOR REVISION HISTORY	

TITLE QUICKNET SFQ SERIES CASSETTE, 4-1 DUPLEX LC TO MPO BREAKOUT CASSETTE CUSTOMER DRAWING					
ITEM REVISION NAME 13F244AK/02					
DATASET FILE NAME 13F244AK_DC/02A					
ALL DIMENSIONS ARE FOR REFERENCE					PART NO. SEE TABLE
 THIRD ANGLE PROJECTION					DRAWING NUMBER: 13F244AK-DC
DRAWN BY BSN	DATE 07-26-16	CHK EJK	SCALE 1:2	SHT 3 OF 3	
					SIZE A