

4

D

C

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	ν. Υ		νν B			×× C ××				
	TYPE	COLOR	TYPE	COLOR	─ DIM "L" (mm/IN)	COLOR	DESCRIPTION			
LPCA01-X	C14	RED	C13	BLACK	24"/609.6mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 2 FEET, 10 PK, RED			
LPCA02-X	C14	RED	C13	BLACK	48‴/1,219.2mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 4 FEET, 10 PK, RED			
LPCA03-X	C14	RED	C13	BLACK	72‴/1,828.8mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 6 FEET, 10 PK, RED			
LPCA04-X	C14	RED	C13	BLACK	96"/2,438.4mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 8 FEET, 10 PK, RED			
LPCA05-X	C14	RED	C13	BLACK	120"/3,048mm	RED	LOCKING POWER CORD, IEC C14 TO IEC C13, 10 FEET, 10 PK, RED			
LPCA06-X	C14	BLUE	C13	BLACK	24"/609.6mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 2 FEET, 10 PK, BLUE			
LPCA07-X	C14	BLUE	C13	BLACK	48"/1,219.2mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 4 FEET, 10 PK, BLUE			
LPCA08-X	C14	BLUE	C13	BLACK	72"/1,828.8mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 6 FEET, 10 PK, BLUE			
LPCA09-X	C14	BLUE	C13	BLACK	96"/2,438.4mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 8 FEET, 10 PK, BLUE			
LPCA10-X	C14	BLUE	C13	BLACK	120"/3,048mm	BLUE	LOCKING POWER CORD, IEC C14 TO IEC C13, 10 FEET, 10 PK, BLUE			
LPCA11-X	C14	BLACK	C13	BLACK	24"/609.6mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 2 FEET, 10 PK, BLACK			
LPCA12-X	C14	BLACK	C13	BLACK	48"/1,219.2mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 4 FEET, 10 PK, BLACK			
LPCA13-X	C14	BLACK	C13	BLACK	72‴/1,828.8mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 6 FEET, 10 PK, BLACK			
LPCA14-X	C14	BLACK	C13	BLACK	96"/2,438.4mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 8 FEET, 10 PK, BLACK			
LPCA15-X	C14	BLACK	C13	BLACK	120"'/3,048mm	BLACK	LOCKING POWER CORD, IEC C14 TO IEC C13, 10 FEET, 10 PK, BLACK			
LPCB01-X	C20	RED	C19	BLACK	24‴/609.6mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 2 FEET, 10 PK, RED			
LPCB02-X	C20	RED	C19	BLACK	48‴/1,219.2mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 4 FEET, 10 PK, RED			
LPCB03-X	C20	RED	C19	BLACK	72‴/1,828.8mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 6 FEET, 10 PK, RED			
LPCB04-X	C20	RED	C19	BLACK	96"/2,438.4mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 8 FEET, 10 PK, RED			
LPCB05-X	C20	RED	C19	BLACK	120"/3,048mm	RED	LOCKING POWER CORD, IEC C20 TO IEC C19, 10 FEET, 10 PK, RED			
LPCB06-X	C20	BLUE	C19	BLACK	24‴/609.6mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 2 FEET, 10 PK, BLUE			
LPCB07-X	C20	BLUE	C19	BLACK	48"/1,219.2mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 4 FEET, 10 PK, BLUE			
LPCB08-X	C20	BLUE	C19	BLACK	72‴/1,828.8mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 6 FEET, 10 PK, BLUE			
LPCB09-X	C20	BLUE	C19	BLACK	96"/2,438.4mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 8 FEET, 10 PK, BLUE			
LPCB10-X	C20	BLUE	C19	BLACK	120"/3,048mm	BLUE	LOCKING POWER CORD, IEC C20 TO IEC C19, 10 FEET, 10 PK, BLUE			
LPCB11-X	C20	BLACK	C19	BLACK	24"/609.6mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 2 FEET, 10 PK, BLACK			
LPCB12-X	C20	BLACK	C19	BLACK	48"/1,219.2mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 4 FEET, 10 PK, BLACK			
LPCB13-X	C20	BLACK	C19	BLACK	72"/1,828.8mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 6 FEET, 10 PK, BLACK			
LPCB14-X	C20	BLACK	C19	BLACK	96"/2,438.4mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 8 FEET, 10 PK, BLACK			
LPCB15-X	C20	BLACK	C19	BLACK	120"/3,048mm	BLACK	LOCKING POWER CORD, IEC C20 TO IEC C19, 10 FEET, 10 PK, BLACK			

3	2
	 NC 1 .
	2.
	3.

	ES: Identificat
	<u>part no.</u> See table
2.	PART SPECIF RATING: C14, C20,
	CABLE: SJT / RoHS COMPLI/ COMPLIANCE / CE, UL, VDE PRIMARY DIME IN [MILLIME

00A	04/08/2021	PJST	GLM	JAWI	RELEASED TO PR
REV	DATE	BY	СНК	APR	

TION: LOCKING POWER CORDS

FICATION: 4/C13 - 10A / 250V AC 20/C19 - 16A / 250V AC AND HO5VV-F (17AWG OR EQUAVALENT) 3 CONDUCTOR, 105°C IANT. E APPROVALS: DE, TUV MENSIONS ARE IN INCHES, SECONDARY DIMENSIONS ARE METERS 1

D

1

			THAT YOU CHECK ONS, NOTES, AND JTE BOX. WILL NOT PROGR APPROVAL. PLEAS JRNING PROOF AS JY.					A	
				LOCI	KING POW	ER (CORD		
		CUSTOMER DRAWING							
		ITEM REVISION NAME 02416LPC/00							
		DATASET FILE NAME 02416LPC_DC/00A UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					FARDUIT		
		. × . . ××.		.XXX ±			N/A		
RODUCTION	02416LPC] {			IRD ANGLE		ving number: 02416LPC_DC		
DESCRIPTION	ECN	DRAWN BY PJST	04/08/2021	снк GLM	NTS		SHT 1 OF 1		

1