
| THIS COPY IS PROVIDED ON | A RESTRICTED BASIS AND IS NOT TO BE U | JSED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. |
|--------------------------------------|--|---|
| Material | High Conductivity Seamless Copper Tube | |
| Plating | Electro-Tin | / 1.06 R Re |
| Wire Size | 650 STR/FLEX | 1.50 K K |
| Wire Type | Stranded Copper: Locomotive | 1.95±.04 (S) 218/HEX AX650-58 |
| Wire Strip Length | 1-1/2 in. | PANDUI PANDUI |
| Stud Size | 5/8 in. | PAP BAP |
| UL Listed Wire Connector | Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts. | .88±.0766±.02 DIA |
| UL Temperature Rating | 90°C | 4.20±.09 |
| C.S.A Certified Wire Connector | Yes | |
| Panduit Color Code on Barrel | BLACK | - 1.45 |
| Panduit Die Index No. on Barrel | P106 | Wire inspection window |
| Alternate Industry Die Index No. () | (24) | |





on Barrel



| | | | | | | PANDUIT CORP. TINLEY PARK, ILLINOIS |
|-----|------|------|------|--|-----|---|
| 01 | 4/09 | JHNU | JHNU | REVISED TOLERANCES: HOLE OFFSET WAS .04, BARREL LENGTH WAS .04 OVERALL LENGTH WAS .06 | | LCAX650-58-6 Copper Lug - One-Hole, Standard Flex Barrel |
| REV | DATE | BY | СНК | DESCRIPTION | ECN | SCALE N/A DRAWING NO / CAD FILE LCAX650-58-CUST |