

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT P/N  | WEIGHT      |
|--------------|-------------|
| P24F##M-XXYZ | SEE SHEET 2 |

**SPECIFICATION:**

- STANDARD
  - UNIT TYPE: MONITORED OUTLET
  - ORIENTATION: VERTICAL, 0U FULL
  - OUTLET QTY & TYPE: SEE SHEET 2 FOR CONFIGURATIONS
  - INPUT VOLTAGE: 200-240/346-415VAC
  - INPUT CURRENT: 30A (24A DERATED)
  - BREAKER QTY & TYPE: (6) 20A, SINGLE POLE
  - INPUT PHASE: THREE-PHASE WYE
  - RATED POWER: 17.3 kVA
  - INPUT PLUG: SEE SHEET 2 FOR CONFIGURATIONS
  - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE

REGULATORY STANDARD: RoHS COMPLIANT

- ADDITIONAL:
  - CIRCUIT BREAKERS RATED AT 10KAIC


- ACCESSORIES:
  - (1) QUICK-START GUIDE

**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PRODUCT
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P24F##M - XXYZ**



FOUR CHARACTER SUFFIX FOR ALTERNATE PRODUCT CONFIGURATIONS

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN \_\_\_\_\_  
 DATE \_\_\_\_\_  
 PRINT \_\_\_\_\_

TITLE: INTELLIGENT SERIES PDU  
**P24F##M-XXYZ**  
 CUSTOMER DRAWING

ITEM REVISION NAME: \_\_\_\_\_  
 DATASET FILE NAME: \_\_\_\_\_





UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm [IN]

Tolerance (mm)  
 0<L<50 ±0.5  
 50<L<250 ±1.0  
 250<L<500 ±1.5  
 500<L<1000 ±2.5  
 1000<L<5000 ±4.0

MATERIAL: \_\_\_\_\_  
 DRAWING NUMBER: **P24F\_DC**

BY: WAC DATE: 03/14/19 CHK: - SCALE: NTS

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.



**PLUG/ RECEPTACLE BLOCK**

|  |  |  |  |
|--|--|--|--|
|  | IEC 60309, 4P 5W, 6H IP67 (WATERTIGHT) 30A, 346-415V MAX RATED INPUT 24A DERATED |  | IEC 60320/C19 16A, 250V MAX RATED OUTPUT |
|  | IEC 60309, 4P 5W, 6H IP44 (SPASHPROOF) 30A, 346-415V MAX RATED INPUT 24A DERATED |  | IEC 60320/C13 10A, 250V MAX RATED OUTPUT |
|  | NEMA L22-30P, 4P 5W 30A, 277-480V MAX RATED INPUT 24A DERATED                    |  |  |

| 01A | 3/19/2019 | WAC | DACU | JAWI | RELEASED TO PRODUCTION | P24F |
|-----|-----------|-----|------|------|------------------------|------|
| REV | DATE      | BY  | CHK  | APR  | DESCRIPTION            | ECN  |

B

B


A

A

D10100DB/17

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| FINISHED GOOD PART NUMBER | FINISHED GOOD DESCRIPTION  | INPUT PLUG CONFIGURATION               | RECEPTACLE CONFIGURATION | COLOR            | INPUT CORD LENGTH                | WEIGHT |
|---------------------------|--|--|--------------------------|------------------|----------------------------------|--------|
| <b>P24F10M</b>            | VERTICAL, (12)C13, (12)C19, MONITORED OUTLET, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK | L22-30P 30A 4P, 5W                     | (12) C13, (12) C19       | BLACK (RAL 9005) | 3M(+254MM/-127MM) 10' [+10"/-5"] | 12.5kg |
| P24F09M                   | VERTICAL, (12)C13, (12)C19, MONITORED OUTLET, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK | IEC60309 30A 4P, 5W, IP67 (WATERTIGHT) | (12) C13, (12) C19       | BLACK (RAL 9005) | 3M(+254MM/-127MM) 10' [+10"/-5"] | 12.5kg |
| P24F13M                   | VERTICAL, (12)C13, (12)C19, MONITORED OUTLET, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK | IEC60309 30A 4P, 5W, IP44 (SPASHPROOF) | (12) C13, (12) C19       | BLACK (RAL 9005) | 3M(+254MM/-127MM) 10' [+10"/-5"] | 12.5kg |
| P24F16M                   | VERTICAL, (18) C13, (6)C19 MONITORED OUTLET, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK  | L22-30P 30A 4P, 5W                     | (18) C13, (6) C19        | BLACK (RAL 9005) | 3M(+254MM/-127MM) 10' [+10"/-5"] | 12.5kg |
| P24F11M                   | VERTICAL, (18) C13, (6)C19 MONITORED OUTLET, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK  | IEC60309 30A 4P, 5W, IP67 (WATERTIGHT) | (18) C13, (6) C19        | BLACK (RAL 9005) | 3M(+254MM/-127MM) 10' [+10"/-5"] | 12.5kg |
| P24F14M                   | VERTICAL, (18) C13, (6)C19 MONITORED OUTLET, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK  | IEC60309 30A 4P, 5W, IP44 (SPASHPROOF) | (18) C13, (6) C19        | BLACK (RAL 9005) | 3M(+254MM/-127MM) 10' [+10"/-5"] | 12.5kg |
| P24F17M                   | VERTICAL, (24) C13, MONITORED OUTLET, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK         | L22-30P 30A 4P, 5W                     | (24) C13                 | BLACK (RAL 9005) | 3M(+254MM/-127MM) 10' [+10"/-5"] | 12.5kg |
| P24F12M                   | VERTICAL, (24) C13, MONITORED OUTLET, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK         | IEC60309 30A 4P, 5W, IP67 (WATERTIGHT) | (24) C13                 | BLACK (RAL 9005) | 3M(+254MM/-127MM) 10' [+10"/-5"] | 12.5kg |
| P24F15M                   | VERTICAL, (24) C13, MONITORED OUTLET, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK         | IEC60309 30A 4P, 5W, IP44 (SPASHPROOF) | (24) C13                 | BLACK (RAL 9005) | 3M(+254MM/-127MM) 10' [+10"/-5"] | 12.5kg |



WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN \_\_\_\_\_  
DATE \_\_\_\_\_  
PRINT \_\_\_\_\_

TITLE  
**INTELLIGENT SERIES PDU**  
**P24F##M-XXYZ**  
CUSTOMER DRAWING

ITEM REVISION NAME \_\_\_\_\_  
DATASET FILE NAME \_\_\_\_\_

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm [IN]

Tolerance (mm)  
0<L<50 ±0.5  
50<L<250 ±1.0  
250<L<500 ±1.5  
500<L<1000 ±2.5  
1000<L<2000 ±4.0

THIRD ANGLE PROJECTION

MATERIAL: \_\_\_\_\_  
DRAWING NUMBER: **P24F**

BY WAC DATE 03/14/2019 CHK NTS SCALE SHEET 2 OF 2 SIZE B

| 01A | 3/19/2019 | WAC | DACU | JAWI | RELEASED TO PRODUCTION | P24F |
|-----|-----------|-----|------|------|------------------------|------|
| REV | DATE      | BY  | CHK  | APR  | DESCRIPTION            | ECN  |

D:01.00DB/17