




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT P/N | WEIGHT |
|-------------|------------------------------|
| FAF80** | .075 LB/EACH 34.08 g/EACH |

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN () ARE IN METRIC.
4. PART INCLUDES:
1- MOUNTING FRAME
1- FACEPLATE COVER
2- M0.7X25mm PAN HEAD MOUNTING SCREWS




| | | | |
|------------------|-------------------|------|---|
| MODEL FILENAME | 10M224AC/01 | SIZE | A |
| DRAWING FILENAME | 10M224AC_DC02/01A | | |

80mm X 80mm FACEPLATE FOR USE WITH 45mm ADAPTERS CUSTOMER DRAWING

PANDUIT[®]
TINLEY PARK, IL 60487

| | |
|--------------------------|-------------|
| I.I. NUMBER | |
| PRODUCT SPEC/ PKG SPEC | |
| ASSY METHOD/ TEST METHOD | |
| SCALE | NONE |
| PART NO. | FAF80** |
| DRAWING NO. | 10M224AC-02 |



ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±.010(.3)
(.XX) ±.031(.8) ANGLES ±

| | |
|----------|---------|
| DRAWN BY | BJN |
| DATE | 6-21-11 |
| CHK'D | JSP |

| | |
|------------------------|-----|
| REVIEW DRAWING NUMBERS | |
| MAT'L | ABS |

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP | OTH |
|-----|---------|-----|-----|------------------------|-------------|-----|------|-----|-----|
| R | 6-21-11 | BJN | JSP | RELEASED TO PRODUCTION | 10M224AC-02 | JSP | JSP | | |