


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ITEM NO.	NAME	DESCRIPTION	QTY.
1	CASE	TDP43ME-CASE CARRYING CASE FOR TDP43ME PRINTER AND SUPPLIES	1
2	LABEL ROLL	ROLL OF S100X150VATY SELF-LAMINATING LABELS	1
3	CLEANING PEN	THERMAL PRINTHEAD CLEANING PEN	1
4	KNIFE	SNAP-BLADE STYLE KNIFE	1
5	POWER SUPPLY	24 VOLT POWER SUPPLY	1
6	COMMUNICATION CABLE	USB CABLE	1
7	POWER CORD	NORTH AMERICAN POWER CORD	1
8	INK RIBBON	RMEH4BL HYBRID INK RIBBON (BLACK)	1
9	CORE	EMPTY RIBBON TAKE UP SPOOL	1
10	USER MANUAL	PRINTER USER MANUAL AND QUICK START GUIDE	1
11	SPINDLE	RIBBON SPINDLE	2
12	MANDREL AND SIDE PLATES	MANDREL AND SIDE PLATES (2) FOR USE WITH EXTERNAL ROLL STAND	1
13	ROLL STAND BASE	ROLL STAND BASE	1
14	LABEL MANDREL	TDP43ME LABEL MANDREL	1
15	SIDE PLATES	TDP43ME LABEL MANDREL SIDE PLATE	2
16	PRINTER	TDP43ME PRINTER	1
17	EASY-MARK PLUS CD	CD WITH EASY-MARK PLUS LABELING SOFTWARE	1
18	DRIVER AND MANUAL CD	CD WITH PRINTER DRIVER AND USER MANUAL	1
19	THERMAL TRANSFER LINE CARD	BROCHURE FOR PANDUIT THERMAL TRANSFER LABELS	1

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

PART NUMBER		TDP43ME-KIT		
TITLE		TDP43ME-KIT Desktop Printer Kit CUSTOMER DRAWING		
ITEM REVISION NAME		I00109BP/04		
DATASET FILE NAME		I00109BP_DC-04A C11743-TDP43ME-KIT r04A CUST DWG		
MATERIAL		NTS		
DRAWING NUMBER		C11743		
DRAWN BY		DATE	CHK	SCALE
RVU		1/14/2021	MSAD	NONE
SHEET 1 OF 1		A		

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	4/21/2022	RVU	ANRO	MSAD	REPLACED FROM IDLC06--SA-ENG TO THERMAL TRANSFER LINE CARD. SEE ITEM NO. 19, VIEW IMAGE. UPDATED ALL NAME BOM. DRAWING TABLE COLUMN HEADING PART NUMBER REPLACED WITH NAME HEADING. ADDED NOTE 2 FOR RoHS.	GAECN06172
00	2/25/2021	RVU	BMAG	RCMC	INITIAL RELEASE	GAECN05851

A-SIZE CUSTOMER

2

1

2

1