





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT
GPB2884R4WJY	2.88 LB/ea (1310 g/ea)

NOTES:

1. THE RACK MOUNT PANEL ASSEMBLY IS DESIGNED FOR MOUNTING TO UNIVERSAL 19" RACKS.
2. FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) METRIC M6x1x15MM SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
3. EACH ASSEMBLY INCLUDES (72) FOUR-PAIR GP6 PLUS CONNECTOR BLOCKS, (4) LABEL HOLDERS, AND (4) LABELS.
4. DIMENSIONS IN BRACKETS ARE METRIC.



PART NUMBER		GPB2884R4WJY	
TITLE			
HIGH DENSITY GP6 PLUS 4RU 19" RACK MOUNT PANEL WITH JUMPER TROUGHS			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479LH/02	
DATASET FILE NAME		M02479LH_DC295_00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .xx ± .03 [.8]		TROUGHS/BASES/WIRESTRIPS: POLYCARBONATE	
.xxx ± .010 [.3]		PANEL: 16 GAUGE C.R.S.	
ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		02479-295	
DRAWN BY	DATE	CHK	SCALE
NER	3-21-06	WJC	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	6-04-14	MDJR	REFR	MMR	A. UPDATED TITLE BLOCK.	02479-295
R	3-21-06	NER	WJC	RMD	RELEASED TO PRODUCTION	02479-295

D10100DA/14