

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| Material | High Conductivity Seamless Copper Tube | | |
|--|--|--|--|
| Plating | Electro-Tin | | |
| Wire Size | 250 kcmil | | |
| Wire Type | Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric | | |
| Wire Strip Length | 1-11/16 in. | | |
| Stud Size | 1/2 in. | | |
| UL Listed Wire Connector | Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts. | | |
| UL Temperature Rating | 90° C | | |
| C.S.A Certified Wire Connector | Yes | | |
| Panduit Color Code on Barrel | YELLOW | | |
| Panduit Die Index No. on Barrel | P62 | | |
| Alternate Industry Die Index No. () on Barrel | (16) | | |









| | | | | | | | | CORP. TINLEY PARK, ILLINOIS |
|-----|------|------|------|------------------|--------|-----|-----|--|
| | | | | | | | | LCB250-12W-X |
| 00 | 4/17 | JHNU | JHNU | DRAWING RELEASED | 019765 | RGB | RGB | Copper Lug - One-Hole, Long Barrel with Window |
| REV | DATE | BY | СНК | DESCRIPTION | ECN | -R | SUP | SCALE N/A DRAWING NO / CAD FILE LCB250-12W-X |