


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:
 1. SEE MFG. DRAWING NO. A61257.
 2. MILLIMETER ARE IN ().

PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER SHEET	SHEETS PER PKG.	LABELS PER PKGS.
N100X150FJJ	GMPO	1,000 [25.4] X 1,500 [38.1]	42	60	2500

CAD FILENAME/LAYERS I00472JQ_C10294_N100X150FJJ_00.PRT

PANDUIT CORP TINLEY PARK, ILLINOIS
 OPTIMUM N100X150FJJ
 LASER/INKJET PRINTABLE LABELS

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± .031 (.XXX) ± .005
 (.XX) ± .015 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN IN
 INCHES, THIRD ANGLE PROJECTION

DRAWN BY: RVU	MAT'L:	SCALE: NTS
DATE: 10-1-04	SEE TABLE	DRAWING NO. C10294
CHK'D:		ORIG. SIZE: B

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
0	10-1-04	RVU		DRAWING RELEASED.	0000	R		