

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	DIM A TARGET (OD) TOL. ±0.008 [±0.20]	DIM B TARGET (ID) TOL. ±0.008 [±0.20]	WALL THICKNESS	QUANTIY FEET PER BOX TOL. +/-3%	
CLT75PUV-0	0.984 [25.00]	0.811 [20.60]	0.018-0.024 [0.45-0.61]	4,265 [1,300 m]	
CLT100PUV-0	1.358 [34.49]	1.142 [29.01]	0.020-0.026 [0.50-0.66]	2,329 [710 m]	
CLT150PUV-0	1.673 [42.49]	1.417 [36.00]	0.020-0.027 [0.52-0.68]	1,542 [470 m]	
CLT188PUV-0	2.146 [54.51]	1.890 [48.01]	0.021-0.028 [0.54-0.70]	885 [270 m]	





PART NUMBER

TITLE

NOTES:

В

Α

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.

2

- 2. DIMENSIONS IN [] ARE METRIC.
- 3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF ROHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITEE.
- 4. ALL PART NUMBERS HAVE ONE CONTINUOUS SLIT ALONG THE ENTIRE LENGTH OF TUBING.
- 5. PRODUCT MAY CONTAIN UP TO 1 SPLICE PER ROLL.
- 6. PRODUCT TESTED TO UL 94 HB FLAME TEST STANDARD.

UV RESISTANT CORRUGATED LOOM TUBING

1

SEE TABLE

В

Α

								CUSTOMER DRAWING					
								ITEM REVIS		IBM/00			
								DATASET FILE NAME 12B061BM_DC/00A					
~								1		TH	RD ANGLE		
OMEF										PR	OJECTION	DRAWING NUMBER	
CUST	00	02/10/22	JBN	DAEI	JADE	INITIAL RELEASE	119533	MATERIAL	POLYPRO	OPYLE		128061BM-DC	С
A-SIZE	REV	DATE	ΒY	СНК	APR	DESCRIPTION	ECN	JBN	DATE 02/10/22	DAEI	SCALE NONE	SHEET 1 OF 1	A

2