

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ITEM NUMBER	PART NUMBER	DESCRIPTION	STANDARD PACKAGE QTY.
1	MP100	MP100 PRINTER	1
2	*T100X000VPM-BK	MP CASSETTE, CONTINUOUS TAPE, VINYL, 1.00" W x 25' L, BLACK ON WHITE	1
3	*MP100-IB	RUBBER BUMPER GUARD FOR MP100	1
4	MP-USB	MP100/300 USB PRINTER CABLE	1
5	*MP-ACS-1	120-240 VAC POWER SUPPLY MODULE WITH POWER CORD FOR NORTH AMERICA	1
6	QUICK REFERENCE CARD	PRINTED COPY OF QUICK REFERENCE CARD IN THREE LANGUAGES (EN, FR, SP)	1
7	IMPORTANT INFORMATION	PRINTED COPY OF IMPORTANT SAFETY INFORMATION SHEET	1

**NOTES:**

1. \* DENOTES PANDUIT PART NUMBER THAT CAN BE PURCHASED SEPARATELY.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:				
							PANDUIT MP100 MOBILE THERMAL TRANSFER PRINTER					
							CUSTOMER DRAWING					
							ITEM REVISION NAME					
							00406SBD/00					
							DATASET FILE NAME					
							00406SBD_DC/00B MP100 PRINTER CUST DWG					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]					
							.x ± .1 [ 2.54 ] .xxx ± .005 [ .127 ]					
							.xx ± .01 [ .25 ] ANGLES ± 5 °					
							THIRD ANGLE PROJECTION					
								NONE				
								DRAWING NUMBER:				
								00406SBD_DC				
00B	3/4/2024	RVU	JSUN	MSAD	DRAWING RELEASE TO WEBISTE.	GAECN05552						
00	10/29/19	TMSA	RCMC	JHAC	INITIAL RELEASE.	-						
00B	3/4/2024	RVU	JSUN	MSAD	DRAWING RELEASE TO WEBISTE.	GAECN05552						
00	10/29/19	TMSA	RCMC	JHAC	INITIAL RELEASE.	-						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							TMSA	10/29/19	JHAC	NTS		A

D10100DA/20