Material	High Conductivity Seamless Copper Tube	- Wire inspection			
Plating	Electro-Tin	window			
Wire Size	2/0 AWG	window by the state of the stat			
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric				
Wire Strip Length	1-9/16 in.	.39±.04			
itud Size	3/8 in.	041.04			
JL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.84±.04			
JL Temperature Rating	90° C	.13±.01 90°±5°			
C.S.A Certified Wire Connector	Yes				
Panduit Color Code on Barrel	BLACK	2.15 REF			
Panduit Die Index No. on Barrel	P45	1.50±.04			
Alternate Industry Die Index No. () on Barrel	(13)	BLACK DIE P45			
	(UL)	.45±.01 Color code barrel markin			
CERTIFIED	LISTED Wire Connector	.58±.01 entry			

RE	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCB2/0-38WF-CUST
00	4/17	JHNU	JHNU	DRAWING RELEASED	021775	Copper Lug - One-ноie, Long Bairei Wiln Window, 90- Angle Tongue
						LCB2/0-38WF-X Copper Lug - One-Hole, Long Barrel with Window, 90° Angle Tongue
						CORP. TINLEY PARK, ILLINOIS

— 1.66 REF –