


Part Number: PCD4B

Product Description: CONDUIT CLAMP FOR 1-1/2" RIGID/IMC WITH NUT AND BOLT AND PLAIN MOUNTING HOLE

**Material Specifications**

Type: Steel

Finish: Zinc Plated

Color: Silver

Function Specifications**Compatible Wires and Cables**

AC/MC CABLE (OD):

Drop Wire:

Plain Rod (in):

Threaded Rods and Bolts

Tapped Holes:

Clearance Holes (in): 5/16

Threaded Rod Size (in):

Compatible Conduit

EMT Size (in):

Rigid/IMC (in): 1-1/2

Compatible Flanges and Studs

Flange Size (in):

Metal Stud Size (ins):

Static Load Rating

Vertical (lbs):

Horizontal (lbs):

Other**Codes and Regulatory**Regulatory
Certifications: UL/cUL

Country of Origin: US

Packaging

General Packaging: Cardboard Box

Box Size: 15 X 8.25 X 7.25

Pieces per Package: 100

Other Box Features:

Document Information

Created By: DBLA

Checked By: DJW

Approved By: KLN

Customer Specification #: C11111

Revision Level: 01

ECN #: GAECN01482

Date: 12/10/2013