


	THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.	
--	--	--

Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		
Wire Size	750 kcmil		
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		
Wire Strip Length	1-15/16 in.		
Stud Size	5/8 in.		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90° C		
C.S.A Certified Wire Connector	N/A		
Panduit Color Code on Barrel	BLACK		
Panduit Die Index No. on Barrel	P106		
Alternate Industry Die Index No. () on Barrel	(24)		









REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A	DRAWING NO / CAD FIL
00	6/17	JHNU	JHNU	DRAWING RELEASED	022679	Copper Lug - Two-H	iole, Standard B
							LCD750-58GH
							CORP.
							57

.26±.01 -

CORP. TINLE	Y PARK, ILLINOIS
-------------	------------------

6H-6 I Barrel, 45° Angle Tongue

FILE N/A

LCD750-58GH-CUST