

MANUAL RELEASE LEVER

5-POSITION ROTATING DIE

NOTES, UNLESS OTHERWISE SPECIFIED:

PANDUIT CT-1701 TOOL:

TOOL WEIGHT: 20 oz. [0,56] kg

Crimps Panduit #10 - #2 AWG non-insulated P series terminals and #14 - 10 AWG copper code conductor lugs. Includes 5-position, rotating die.

Provides UL Listed and CSA Certified terminations with applicable Panduit terminals.

DIMENSIONS SHOWN IN BRACKETS [] ARE METRIC, AND ARE FOR REFERENCE ONLY.

	ENG	SLISH	METRIC			
DIE	GO / NO	GO GAGE	GO / NO GO GAGE MEMBERS			
INDEX	MEN	/IBERS				
NUMBER	"G" Dia.	"NG" Dia.	"G" Dia.	"NG" Dia.		
	(GO)	(NO GO)	(GO)	(NO GO)		
P10	0.099"	0.109"	2,51 mm	2,76 mm		
P8	0.179"	0.201"	4,54 mm	5,10 mm		
P6	0.217"	0.238"	5,51 mm	6,04 mm		
P4	0.273"	0.295"	6,93 mm	7,49 mm		
P2	0.351"	0.374"	8,91 mm	9,49 mm		

							CT-1701 Contour Crimp TM Crimping Tool CUSTOMER DRAWING			
							TP2382		02	PANDUIT
					ADDED GO – NO GO CHART.		UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL:	
02	2-10-17	BLR	BJPU	JADE	REMOVED GLOBAL LOGO FROM GRIP, MOVED MADE IN GERMANY TO FRAME.	4857/02	` '	xxx) ± NGLES ±		
01	5-08-15	BLR	BJPU	ABJ	REDRAWN; UPD BRANDING	4857	THIRD ANGLE PROJECTION		DRAWING NUMBER: TP23827C01	
REV	DATE	ВҮ	СНК	APR	DESCRIPTION	ECN	DRAWN BY: DATE BLR 5-08-	_		SHT 1 OF 1 SIZE