



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
2. DIMENSIONS IN PARENTHESIS ARE METRIC.
4. UNIT IS MADE FROM 14 GAUGE ALUMINUM.
5. ENCLOSURE IS PAINTED BLACK.
6. PART CAN ACCOMODATE 12 MINI-COM MODULES AND 4 POWER PORTS.
7. ENCLOSURE IS SUPPLIED WITH (1) HARDWARE KIT WHICH INCLUDES:
 - 2-GROMMETS
 - 4-TAK-TYS
 - 1-GROUNDING WIRE
 - 2-#10 WASHER
 - 2-#10-32 HEX NUT
 - 2-6 POSITION FACE PLATES
 - 1-PORT I.D. LABEL
 - 2-LABEL COVERS



PANDUIT PART NO.	WEIGHT
CUFMB12D4PBL	2.2 LBS/EACH 998 g/EACH



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	2-6-15	BAME	NAGL	KRKE	UPDATED TITLE BLOCK	10573-07
01	10-15-07	JLGI		BAS	RELEASED TO PRODUCTION	10573-07
00	10-15-07	JLGI		BAS	RELEASED TO DESIGN APPROVAL	10573-07

TITLE		UNDER FLOOR MODULAR BOX W/12 DATA AND 4 POWER PORTS (CUFMB12D4PBL)	
CUSTOMER DRAWING			
ITEM REVISION NAME	V10573AA/01	PANDUIT	
DATASET FILE NAME	V10573AA_DC/01A		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.X ±	.XXX ±	SEE NOTES	
.XX ±	ANGLES ±		
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
DRAWN BY: JLGI		10573-07	
DATE: 10-15-07	CHK: BAS	SCALE: NONE	SHT 1 OF 2
		SIZE: A	

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



B

B



A

A

01A	2-6-15	BAME	NAGL	KRKE	UPDATED TITLE BLOCK	10573-07
01	10-15-07	JLGI		BAS	RELEASED TO PRODUCTION	10573-07
00	10-15-07	JLGI		BAS	RELEASED TO DESIGN APPROVAL	10573-07
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					
UNDER FLOOR MODULAR BOX W/12 DATA AND 4 POWER PORTS (CUFMB12D4PBL)					
CUSTOMER DRAWING					
ITEM REVISION NAME			V10573AA/01		
DATASET FILE NAME			V10573AA_DC/01A		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)					
.X ± .XX ±					
.XXX ± ANGLES ±			MATERIAL: SEE NOTES		
			DRAWING NUMBER: 10573-07		
DRAWN BY	DATE	CHK	SCALE		
JLGI	10-15-07	BAS	NONE	SHT 2 OF 2	A

2

1