Adjustable Depth Wall Mount Rack



Adjustable Depth Wall Mount Rack

12, and 18 RU

specifications

The Adjustable Depth Wall Mount Rack shall meet EIA/ECA-310-E standards, be available in 9, 12, or 18 RU, constructed of steel and capable of accepting 19" wide EIA equipment. The rack shall have adjustable depth of 18", 21.5", or 25". The equipment mounting rails shall be #12-24 threaded style mounting. The equipment mounting rails shall include printed rack unit numbering from bottom up. The rack shall accept shelve units and equipment brackets. Side rails slots shall be designed to accommodate Tak-Ty, which can be used for cable management. Bend radius control accessories shall be installed on the front rail to further manage cable routing. The construction method shall allow for single person installation. The rack shall contain two masked grounding locations to ensure proper bonding and grounding.



technical information

Part Number	RU	Height In. (mm)	Width In. (mm)	Depth In. (mm)
AWMR9	9	16.83 (427.5)	20.31 (515.9)	18 (457.2), 21.5 (546.1), 25 (635)
AWMR12	12	22.43 (569.7)	20.31 (515.9)	18 (457.2), 21.5 (546.1), 25 (635)
AWMR18	18	33.65 (854.7)	20.31 (515.9)	18 (457.2), 21.5 (546.1), 25 (635)

key features and benefits

Adjustable depth:	Supports equipment mounting depths from 18", 21.5", and 25" to provide greater flexibility with a single part number		
Welded steel construction:	ETL approved, meets UL2416 with a tested load capacity of 150 lbs. for the 9 and 12 RU, 200 lbs. for the 18 RU		
Self-squaring:	Design allows for single person installation		
Key features:	Horizontal slots on the adjustable wall attachment brackets are compatible with Tak-Ty and allow for easy front to back cable management		
Color options:	Available in Black		
Numerical rack unit identification:	Allows for quick location of rack spaces speeding installation of rack mount items, racks are numbered from bottom up		
Fully bonded structure:	Paint piercing hardware electrically bonds the rack when assembled, eliminating the need for additional bonding components		
Integrated masked grounding locations:	Two masked grounding locations available for customizable configurations		

•, •=, ••••••					
9 RU:	AWMR9				
12 RU:	AWMR12				
18 RU:	AWMR18				
Adjustable Depth Wall Mount Rack Accessories					
StructuredGround [™] equipment bonding jumper:	RGCBNJ460P				
StructuredGround [™] equipment bonding jumper kit:	RGCBNJ660P22				
Shelves					
19"W × 15.2"D:	SRM19FM1				
100 #12-24 screws:	S1224-C				
Cable Management					
5 RU finger section 5" depth:	CMBRC5E				
5 RU finger section 3" depth:	CMBRC5				
1 RU clip 5" depth:	CMBRC1E				
1 RU clip 3" depth:	CMBRC1				
3" bend radius post:	PZBR3				
4" bend radius post:	PZBR4				
Horizontal Cable Manager					
2 RU single-sided:	NMF2				
2 RU dual-sided:	NM2				
Patch Panels					
24-port:	CPPL24WBLY				
48-port:	CPPL48WBLY				

applications

The Adjustable Depth Wall Mount Rack is designed to support network equipment found in data center, telecommunication room and lab environments. The rack is wall mountable providing the user with maximum flexibility when designing the network layout. Front weldments with adjustable front-to-back braces provide the required strength and flexibility needed to work with various types of active equipment. The open design allows for maximum airflow in and around the rack. The Adjustable Wall Mount rack offers flexibility to work with many different designs and application needs.

Adjustable Depth Wall Mount Rack



- 1. Vertical Channels #12-24 tapped holes with rack space numbering
- 2. Steel Wall Mount Rack Depth Adjustable depths of 18", 21.5" & 25"
- 3. Masked Area For Grounding On Each Side
- 4. Cable Management Slots

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

© 2023 Panduit Corp. ALL RIGHTS RESERVED. RKSP194-WW-ENG 7/2023