
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT . PART #	WIRE RANGE		MAX. WIRE	HOUSING	DIMENSIONS in. [mm]				
	ENGLISH	METRIC	INSUL. DIA.	COLOR	A ± (0,8]	B ± .01 [0,3]	C ± .02 [0,3]	D DIA	TOOLS
PV18-P47	22–18	0,5-1,0	.15 [3,8]	RED	.97 [24,6]	.07 [1,8]	.49 [12,4]	.15 [3,8]	CT-100#
PV14-P47	16–14	1,5-2,5	.17 [4,3]	BLUE	.97 [24,6]	.07 [1,8]	.49 [12,4]	.17 [4,3]	**CT-260 CT-600A (CT-550CH)
PV10-P55*	12–10	4,0-6,0	.25 [6,4]	YELLOW	1.10 [27,9]	.10 [2,5]	.55 [14,0]	.25 [6,35]	CT-1550 CT-1551 CT-2500 (CT-2550CH)



HOUSING

*NOT UL LISTED

**PANDUIT APPROVED TOOL

NOTES:

1. UL LISTED FOR:

A. SOILD OR STRANDED COPPER WIRE ONLY

B. 221°F [105°C] MAX. OPERATING TEMPERATURE

C. 600V. MAX. VOLTAGE RATING

2. SEE www.panduit.com FOR PACKAGE QUANTITIES

3. MATERIAL:


A. STAMPING: .03" [0,8] THK COPPER, TIN PLATED

B. HOUSING: VINYL, COLOR CODED

4. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT

5. WIRE STRIP LENGTH: 5/16" +1/32 [7,9 +0,8]





2