

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.

  2. DIMENSIONS IN [] ARE METRIC.
- 3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF ROHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITEE.

TOOL SPECIFIC NOTES:

- 1. THE CT-2980/STBT BATTERY OPERATED TOOLS ARE DESIGNED TO CRIMP WITHOUT CRIMP DIES.
- 2. CRIMPS PANDUIT COPPER AND ALUMINUM COMPRESSION CONNECTORS. GO TO www.panduit.com FOR MORE INFORMATION.
- 3. THIS TOOL CAN OPERATE WITH BLUE TOOTH TECHNOLOGY TO CONNECT TO THE I-PRESS PHONE APP TO MONITOR CRIMP PERFORMANCE.

THE CT-2980/BT TOOL KIT INCLUDES: QTY. DESCRIPTION/ITEM


- BATTERY OPERATED 6.7 TON HYDRAULIC DIELESS CRIMP TOOL
- RECHARGEABLE BATTERIES (MAKITA LI-ION 18VDC, 4Ah) MAKITA BATTERY CHARGER 120VAC (WITH
- US PLUG CONFIGURATION)
- TOOL CASE

TECHNICAL INFORMATION:

- 1. TOOL WEIGHT (INCLUDING BATTERY) 10.8 LBS. [4.9 kg] 2. DIMENSIONS (INCLUDING BATTERY) 15.2" L x 13.8" H x 3.0" W
- [386.5 L x 351 H x 76 W] mm

  3. CRIMPING FORCE VARIABLE TO 6.2 TONS [55 kN]. THIS TOO HAS TWO STAGE HYDRAULIC SYSTEM WITH RAPID ADVANCE AND POWER STROKE.
- 4. A COPY OF OPERATION MANUAL AND ACCESSORY INFORMATION CAN BE FOUND AT: www.panduit.com.

DIMENSIONS IN [BRACKETS] ARE IN MILLIMETERS. ALL DIMENSIONS ARE FOR REFERENCE ONLY.



1-11-22 JHNU JHNU JADE ADDED OSHA NOTE UNDER TOOL VIEW 115032 11-24-21 BJPU JEH JADE RELEASED FOR PRODUCTION 093806 REVI DATE BY CHK APR DESCRIPTION ECN BJPU JEH SHEET 1 OF 1 11-24-21 NONE

 $\mathsf{B}$