

Part Number: P3000037EG

Product Description: MALLEABLE IRON BEAM CLAMP FOR 3/4" FLANGE WITH 3/8 -16 THREADED HOLE



Material Specifications

Type: Assembly

Finish: Cast

Color: Various

Function Specifications

Compatible Wires and Cables

AC/MC CABLE (OD):

Drop Wire:

Plain Rod (in):

Threaded Rods and Bolts

Tapped Holes: 3/8-16

Clearance Holes (in):

Threaded Rod Size (in):

Compatible Conduit

EMT Size (in):

Rigid/IMC (in):

Compatible Flanges and Studs

Flange Size (in): 3/4" (approx. 0.72" openin

Metal Stud Size (ins):

Static Load Rating

Vertical (lbs): 250 Bottom, 500 Top

Horizontal (lbs):

Other

3/8"-16 Nut & Bolt included, 3/8"-16 mounting hole on bottom

Codes and Regulatory

Regulatory Certifications: UL/CUL

Country of Origin: CN

Packaging

General Packaging: Cardboard Box

Box Size: 7.5 X 5.5 X 4.5

Pieces per Package: 25

Other Box Features:

Document Information

Created By: DBLA

Checked By: DJW

Approved By: KLN

Customer Specification #: C11440

Revision Level: 0

ECN #: GAECN01813

Date: 3/19/2014