					2		1		
	THIS CO	IPY IS	5 PRO'	/IDED	ON A RESTRICTED BASIS AND IS NOT TO BE U	SED IN ANY V	WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.		
B	888 [22.0] .345 [8.8] .345 [8.8] .345 [8.8] .345 [8.8]						* PANDUIT P/N WEIGHT GPCB4-XY .08 LB/10 PCS GPCB4-CY .34.3 g/10 PCS *1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY. 2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART. 3. DIMENSIONS IN I J ARE IN METRIC. 4. CATEGORY 6 PERFORMANCE CONNECTOR. 5. INSTALLATION TOOL REQUIRED TO INSTALL BLOCK ONTO BASE. 6. MATERIAL: HOUSING: POLYCARBONATE CONTACTS: PHOSPHOR BRONZE		
	5/30/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-261	PART NUMBER GPCB4-XY gGPCB4-CY TITLE GP6 PLUS CONNECTING BLOCK 4 PAIR CUSTOMER DRAWING ITEM REVISION NAME M02479JZ/01 DATASET FILE NAME M02479JZ_DC261/00B UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .×:		
*1/Va001010	3-20-06	NER	WJC	RMD	RELEASED TO PRODUCTION	02479-261	THIRD ANGLE PROJECTION 02479-261		
	DATE	ΒY	СНК	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE NER 3-20-06 WJC NONE SHT 1 0F 1		
					2		1		