


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FIBER POSITION 12 11 10 9 8 7 6 5 4 3 2 1




PANDUIT P/N	DESCRIPTION
FCZ-12-10BY	50/125 10GbE OM4 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FCZO-12-10BY	OPTIMIZED 50/125 10GbE OM4 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE

NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- MATERIALS:
A. MODULE HOUSING AND COVER: PLASTIC
B. ADAPTER: COMPOSITE PLASTIC
- CASSETTE MODULE WEIGHT: 3.82oz (108.2g)
- DIMENSIONS IN BRACKETS ARE METRIC.


B

METHOD A FLIPPED 12F - CASSETTE (AF)												
MTP END / LC END	FIBER POSITION FROM MTP END TO LC END											
MTP	1	2	3	4	5	6	7	8	9	10	11	12
LC	2	1	4	3	6	5	8	7	10	9	12	11




FRONT VIEW

SHOWN W/O DUSTCAPS



FIBER POSITION

AS VIEWED FROM THE FRONT WITH THE ADAPTERS REMOVED FOR CLARITY



PART NUMBER		FCZ-12-10BY, FCZO-12-10BY	
TITLE			
12 FIBER CASSETTE MODULE METHOD A FLIPPED MTP TO DUPLEX LC CONFIGURATION			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02068AU/00	
DATASET FILE NAME		M02068AU_DC/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.X ±		.XXX ±	
.XX ±		ANGLES ±	
DRAWING NUMBER:		02068-66	
THIRD ANGLE PROJECTION	SHT 1 OF 1		
DRAWN BY	DATE	CHK	SCALE
EFK	9-16-09	TMSE	NONE
REV	DATE	BY	CHK
APR			
DESCRIPTION		ECN	SIZE
		02068-66	A

D10100DA/14