THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. LABEL **CASSETTE** ROLL MP CASSETTE "A" COMPATIBLE WIDTH "B" NOTES: COLOR MATERIAL LENGTH +/-.030 **PRINTERS** PART NO. 1. THESE CASSETTES CONTAIN INK RIBBON AND REF +10% / -0% [0.76]PRINTABLE MEDIA. 2) THE PRODUCTS CAN BE PRINTED WITH 0.229 **BLACK ON** PANDUIT PRINTERS (SOLD SEPARATELY), T024X000FJM-BK [5.82] WHITE AS LISTED IN THE TABLE. 0.87 23 ft MP75, MP100, GMPO4 3) SEE Panduit.com FOR MORE INFORMATION. MP200, MP300 [22.1] [7 m] 0.347 **BLACK ON** T038X000FJM-BK [8.82] WHITE В **←** "∧" → **←** 2.53 [64] **→** 2.95 [75.00] LABEL SIDE **BACKSLIT** LINER-SIDE VIEW TITLE MP POLYOLEFIN TAPE CASSETTE T\*\*X000FJM-BK CUSTOMER DRAWING ITEM REVISION NAME 100743XW/00 DATASET FILE NAME 100743XW\_DC/00A MATERIALS UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ] SEE TABLE .x ± .1 [2.54] .xxx ± .025 [ .635 ] .xx ± .05 [1.27] ANGLES ± THIRD ANGLE 00A 12/16/21 ARHA KJM | MSAD | DRAWING RELEASE. **GAECN06413** I00743XW\_DC **PROJECTION** DRAWN BY DATE SCALE DATE CHK APR DESCRIPTION ECN ΒY ARHA 12/16/21 **MSAD** NTS SHT 1 0F 1 2

В