




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



12 PORT SHOWN



NOTES:

1. SEE CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN BRACKETS ARE METRIC [ mm ].
4. PART INCLUDES:
  - (1) ENCLOSURE PRELOADED WITH (6, 12, 24 or 48) DUPLEX MULTIMODE, SINGLEMODE SC OR E2000 ADAPTERS.
  - (1) HARDWARE KIT CONTAINING:
    - (4) M6 x 12mm SCREWS (10029-01)
    - (4) #12-24 x 1/2" SCREWS (34466-22)
    - (2) FIBER SLACK SPOOL (RFMS1)
    - (1) 2 FIBER ENTRY GROMMETS (00466-02)
    - (1) PG-11 GLAND (00001-141)
    - (2) PAN-TY CABLE TIES (PLT2S-M0)
    - (1) FIBER CAUTION LABEL
    - (1) LASER WARNING LABEL

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
03D	09-21-23	SAT	JSP	ANJA	F. ADDED P/N's FD1W12LMDLCZ, FD1W24LMDLCZ & FD1W48LMDLCZ.	F10431AJ-DC
03C	12-14-22	SAT	JSP	ANJA	E. ADDED P/N's FD1W48AQDLCZ, FD1W48AGDLCZ & FD1W48EIDL CZ.	F10431AJ-DC
03B	10-18-22	SAT	JSP	ANJA	D. ADDED P/N's FD1W6E1DSCZ, FD1W6AGDSCZ, FD1W12E1DSCZ, FD1W12AGDSCZ, FD1W24E1DSCZ, FD1W24AGDSCZ, FD1W12E1DLCZ, FD1W12AGDLCZ, FD1W24E1DLCZ, FD1W24AGDLCZ.	F10431AJ-DC
03A	07-14-22	SAT	JSP	ANJA	C. REMOVED E2000 PRODUCT, OBSOLETE. B. REMOVED ALL PHOS BRONZE P/N's. A. ADDED P/N FD1W48BUDLCZ.	F10431AJ-DC
00	03-16-17	SAT	BSN	DFP	RELEASED TO PRODUCTION	F10431AJ-DC

TITLE		FD1 FIBER DRAWER WITH OPTIONAL ADAPTER ASSEMBLY		
ITEM REVISION NAME		F10431AJ/03		
DATASET FILE NAME		F10431AJ_DC/03D		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		PART NO.		
.x ± .xx ± .03 [ 0.8 ]		SEE SHEET 2 & 3		
.xxx ± .010 [ 0.3 ]		DRAWING NUMBER:		
ANGLES ±		F10431AJ-DC		
THIRD ANGLE PROJECTION		SHT 1 OF 3		
DRAWN BY	DATE	CHK	SCALE	SIZE
SAT	3-13-17	BSN	NONE	A



DUPLEX LC					
PART NUMBER	ADAPTER COLOR	SPLIT SLEEVE TYPE	APPLICATION	NUMBER OF PORTS	WEIGHT
FD1W12AQDLCZ	AQUA	ZIRCONIA	50/125 OM3	12	6.5 LBS (2948g)
FD1W12BUDLCZ	BLUE	ZIRCONIA	9/125 OS2		
FD1W12EIDLCZ	ELECTRIC IVORY	ZIRCONIA	62.5/125 OM1		
FD1W12AGDLCZ	APC GREEN	ZIRCONIA	9/125 OS2		
FD1W12LMDLCZ	LIME	ZIRCONIA	50/125 OM5		
FD1W24AQDLCZ	AQUA	ZIRCONIA	50/125 OM3		
FD1W24BUDLCZ	BLUE	ZIRCONIA	9/125 OS2		
FD1W24EIDLCZ	ELECTRIC IVORY	ZIRCONIA	62.5/125 OM1		
FD1W24AGDLCZ	APC GREEN	ZIRCONIA	9/125 OS2		
FD1W24LMDLCZ	LIME	ZIRCONIA	50/125 OM5		
FD1W48AQDLCZ	AQUA	ZIRCONIA	50/125 OM3	48	
FD1W48BUDLCZ	BLUE	ZIRCONIA	9/125 OS2		
FD1W48EIDLCZ	ELECTRIC IVORY	ZIRCONIA	62.5/125 OM1		
FD1W48AGDLCZ	APC GREEN	ZIRCONIA	9/125 OS2		
FD1W48LMDLCZ	LIME	ZIRCONIA	50/125 OM5		


REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
-----	------	----	-----	-----	-------------	-----

TITLE			
FD1 FIBER DRAWER WITH OPTIONAL ADAPTER ASSEMBLY			
CUSTOMER DRAWING			
ITEM REVISION NAME		F10431AJ/03	
DATASET FILE NAME		F10431AJ_DC/03D	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)			
.x ±	.xxx ± .010 (0.3)	PART NO.	
.xx ± .03 (0.8)	ANGLES ±	SEE SHEET 2 & 3	
DRAWN BY		DRAWING NUMBER:	
SAT	DATE	F10431AJ-DC	
3-13-17	BSN	SHT 3 OF 3	
CHK	SCALE	SIZE	
NONE	A		