

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
HC2**2 (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	0.79 LB (358g)	0.12 LB/FT (1.8g/cm)
HC2**6 (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	0.72 LB (327g)	0.12 LB/FT (1.8g/cm)
HC2**3 (SEE NOTE 1)	118.11 IN ±.18 IN (3000mm ±4.6mm)	1.18 LB (536g)	0.12 LB/FT (1.8g/cm)
HC2**10 (SEE NOTE 1)	120.00 IN ±.18 IN (3048mm ±4.6mm)	1.20 LB (545g)	0.12 LB/FT (1.8g/cm)

**NOTES:**

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	5/11/2021	MES	PATR	PATR	ADDED PART NUMBERS HC2**3, HC2**10	V09002MM/00
1	03-05-13	JBN	RTFI	RN	A. UPDATED DRAWING BORDER & TITLE BLOCK	38258-23
R	01-08-07	MSO	RN	RN	RELEASED TO PRODUCTION	38258-23

TITLE <b>FIBERRUNNER 2X2 HINGED COVER (HC2**2, HC2**6, HC2**3, HC2**10)</b>		<b>PANDUIT</b>
CUSTOMER DRAWING		
ITEM REVISION NAME D38258CH/00		MATERIAL: <b>PVC</b>
DATASET FILE NAME D38258CH_DC/00C		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		DRAWING NUMBER: <b>38258-23</b>
.X ± .XXX ± .XX ± .03 [ .8 ] ANGLES ±		
THIRD ANGLE PROJECTION		
DRAWN BY MSO	DATE 01-08-07	CHK RN
SCALE NONE		SIZE A

2

1

D10100DA/15