

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube				
Plating	Electro-Tin				
Wire Size	250 kcmil				
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric				
Wire Strip Length	1-11/16 in.				
Stud Size	3/8 in.				
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.				
UL Temperature Rating	90° C				
C.S.A Certified Wire Connector	Yes				
Panduit Color Code on Barrel	YELLOW				
Panduit Die Index No. on Barrel	P62				
Alternate Industry Die Index No. () on Barrel	(16)				









									CORP. T	INLEY PARK, ILLINOIS
								LCC250-38DW-X		
01	8/12	JHNU	JHNU	REMOVED NAVY NUMBER	N10883VF-LCC250-38DW-CUST	RGB	RGB	Copper Lug - Two-Hole, Long Barrel with Window		
REV	DATE	BY	СНК	DESCRIPTION	ECN	-R	SUP	SCALE N/A	DRAWING NO / CAD FILE	LCC250-38DW-CUST