PANDUIT®

Next Generation BlackFin Tools

Panduit is launching eight bluetooth electro-hydraulic handheld battery operated BlackFin tools. Crimping wire ranges are from 14 AWG - 1000 kcmil for flex and code wire using all the same crimp dies and inserts from our current generation Blackfin tool offering.

i-press® software and i-press® app

i-press[®] - Show your customers how well you work. Klauke Next Generation records your operations, which can then be transmitted by Bluetooth. The free i-press software uses the data to create a project report, you can use to perfect your quality. **i-press® app** - Use the i-press app to check and control your tool data on the go. Individual tool settings, such as the number of warning tones for an incorrect crimp or the double-click function for increased user safety.

1 LED display

Real time communication of details associated with the tool, including battery charge, pressure level, and cycle information

2 Enhanced housing construction

Internal components of the tool are protected against dirt and water intrusion

3 Reverse tapered hand grip

Increases grip strength and optimal hand positioning to avoid user fatigue

4 Upgraded Power Supply

4.0 Ah battery – Improves power duration and includes battery protection and fuel gauge.3 year warranty included

PANDUIT 2
3
4 makità 101 internation

Key F	eatures
-------	---------

Benefits

Real Time Communication Technology	Access to tool information to increase the efficiency of your work and be more productive			
New Diagnostics	New Bluetooth networked tools interface to diagnose any tool or a fleet of tools to keep optimal overview of inventory			
Improved Safety and Comfort	Updated designs focused on optimizing the tool center of gravity not only allows you to be more comfortable, but also more productive			
Upgraded Power Supply	High capacity 4.0 Ah Li-Ion Makita battery platform with active battery monitoring system improves your battery supply			
LED Display	Real-time communication of details associated with the tool, including battery charge, pressure level, and cycle information			
Enhanced Housing Construction	Protects internal components of the tool against dirt, debris and water intrusion			
Reverse Tapered Hand Grip	Increases grip strength and optimal hand positioning to avoid user fatigue			

PANDUIT[®]

Product Bulletin

	Crimp Force	Part Number	Tool Type	Terminates Panduit Compression Connectors
In Line Type Crimpers	5			
Pure la constantia	4-ton	CT-2600/LBT	Die	 Tin and nickel plated #8 – 2 AWG high temperature large wire, non-insulated, vinyl and KYNAR** insulated ring terminals 8 AWG - 300 kcmil copper Code lugs and splices. 6 AWG - 2/0 AWG Dual rated aluminum lugs and splices
Partie 4000 Min	6.7-ton	CT-3001/STBT	Die	 Copper lugs and splices #8 AWG-600 kcmil code conductor Copper lugs #8 AWG - 313 kcmil flex conductor Aluminum lugs #6 AWG - 350 kcmil code conductor Large Ferrules #1 AWG - 444 kcmil Copper CTAPF taps #10 - 3/0 AWG code conductor Copper CTAP taps #8 - #2 AWG code conductor Copper S Series Tubular Terminals #8 AWG -250 kcmil code conductor Copper Metric lugs and splices for 10mm² - 240mm² class 2R conductor, 10mm² - 95mm² class 5f/6f
	6.7-ton	CT-3001/CCPBT	Die	 Copper lugs and splices #8 AWG - 600 kcmil code conductor Copper lugs #8 AWG - 373 kcmil flex conductor Aluminum lugs #6 AWG - 350 kcmil code conductor Large Ferrules #1 AWG - 444 kcmil Copper CTAPF taps #10 - 3/0 AWG code conductor Copper CTAP taps #8 - #2 AWG code conductor Copper S Series Tubular Terminals #8 AWG - 250 kcmil code conductor Copper Metric lugs and splices for 10mm² - 240mm² class 2R conductor, 10mm² - 95mm² class 5f/6f Cut and Punch Capabilities
Participant and	6.7-ton	CT-3980/BT	Dieless Indenter	 Copper lugs and splices #8 AWG – 600 kcmil code conductor Copper lugs #8 AWG – 373 kcmil flex conductor Aluminum lugs for #6 AWG - 350 kcmil code conductor

PANDUIT®

Product Bulletin

	Crimp Force	Part Number	Tool Type	Terminates Panduit Compression Connectors
Pistol Grip Type Crim	pers			
Contraction of the second	6.2-ton	CT-2980/STBT	Dieless Quad-Point	• Copper lugs and splices #4 AWG – 750 kcmil code conductor • Aluminum lugs and splices #4 AWG – 500 kcmil code conductor
PARLIT	12-ton	CT-2931/STBT	Die	 Copper lugs and splices #8 AWG – 750 kcmil code conductor Copper lugs #8 AWG – 535 kcmil flex conductor Copper S Series, Tubular Terminals #8 AWG – 250 kcmil code conductor Copper Metric lugs and splices 10mm² – 400mm² class 2R conductor 10mm² - 300mm² Class 5f/6f StructuredGround™ Direct Burial connectors #6 AWG – 250 kcmil code conductor and select 500 kcmil conductor combinations Copper CTAPF taps #10 – 3/0 AWG code conductor Copper HTCT taps #14 AWG – 250 kcmil code conductor, #14 - 4/0 AWG flex conductor Aluminum lugs and splices for #6 AWG – 600 kcmil code conductor
Paquet	12-ton	CT-2920/CCPBT	Die	 Copper lugs and splices #8 AWG - 750 kcmil code conductor Copper lugs and splices 4 AWG - 750 kcmil code conductor w/UA12ID dieless indenter adapter accessory Copper lugs #8 AWG - 535 kcmil flex conductor Copper S Series Tubular Terminals #8 AWG - 250 kcmil code conductor Copper lugs and splices 10mm² - 400mm² class 2R conductor, 10mm² - 300mm² Class 5f/6f StructuredGroundTM Direct Burial connectors #6 AWG - 1/0 AWG code conductor Copper CTAP taps #8 - 4/0 AWG code conductor Copper HTCT taps #14 AWG - 2 AWG code conductor Aluminum lugs and splices #6 AWG - 600 kcmil code conductor Aluminum lugs #6 AWG - 600 kcmil code conductor w/UA12ID dieless indenter adapter accessory. Cut and Punch capabilities
	15-ton	CT-2940/STBT	Die	 Copper lugs and splices #8 AWG – 1000 kcmil code conductor Copper lugs #8 AWG – 777.7 kcmil flex conductor Copper S Series Tubular Terminals #8 – 250 kcmil code conductor Copper Metric lugs and splices 10mm² – 630mm² class 2R and, 10mm² - 300mm² Class 5f/6f metric conductor StructuredGround™ Direct Burial connectors #6 AWG – 500 kcmil code conductor Copper CTAPF taps #10 – 3/0 AWG code conductor Copper CTAPF taps #8 – 4/0 AWG code conductor Copper HTCT taps #14 AWG – 250 kcmil code conductor, #14 – 4/0 AWG flex conductor Aluminum lugs and splices #6 AWG – 1000 kcmil code conductor

*For additional information see Tool Specification Guide via www.panduit.com

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300

PANDUIT®

PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 AND SALES OFFICES PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 ©2022 Panduit Corp. ALL RIGHTS RESERVED. Printed in the U.S.A. 04/2022