


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. NOTES: 1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT. 2. FACTORY SETTINGS: ALL DEPTHS: FRONT FACE OF FRONT E-RAILS ARE: 64.0mm ±2.0mm / [2.52in ±0.08in] FROM FRONT FACE OF FRAME. FRONT FACE OF REAR E-RAILS ARE: 742mm ±2.0mm / [29.2in ±0.08in] FROM FRONT FACE OF FRONT E-RAILS. 3. FOR REAR E-RAIL ADJUSTMENTS SEE TABLE ON SHEET 6 4. CAN BE USED WITH ANY 19" EIA B STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS 5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS 15.88mm, 15.88mm, 12.70mm, 15.88mm, 15.88mm, 12.7mm...ETC.
6. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS 7. FRONT TO BACK BEAMS ARE NUMBERED AND INDEXED FOR E-RAIL LOCATIONS 8. PARTS SUPPLIED: -FRAME -E-RAILS -TOP CAP -SIDE PANELS -SINGLE HINGED FRONT DOOR -SPLIT HINGED REAR DOOR -(1) SET OF PDU BRACKETS - (4) LEVELING LEGS -(4) CASTERS 9. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS 10. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM, BOTH FRONT AND BACK OF CABINET 11. STATIC LOAD RATING: 1588 Kg (3500 lbs)
12. ROLLING LOAD RATING: 454 Kg (1000 lbs)
13. PRIMARY DIMENSIONS ARE IN MILLIMETERS 800MM FLEXFUSION™ 800MM FLEXFUSION™ XGL CABINET XGL CABINET FRONT VIEW REAR VIEW TITLE FLEXFUSION™ XGL 800mm CABINET FAMILY CUSTOMER DRAWING ITEM REVISION NAME 01196EAW/00 DATASET FILE NAME 01196EAW_DC/00A MATERIAL: N/A DRAWING NUMBER: MEX-00A 2/21/23 TKW ELE DRAWING RELEASE V09002UV/00 THIRD ANGLE JAGC 01196EAW-DC PROJECTION DRAWN BY DATE SCALE MEX-APR ECN REV DATE CHK DESCRIPTION 2/21/23 TKW NONE SHT 1 0F 6 JAGC








1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

 B

DESCRIPTION	DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"	DIM "F"
	LEVELING LEGS		FLOOR MOUNT		FLOOR OPENING	
FLEX FUSION™ LIMITED 800mm WIDE X 1070mm DEEP	662 (26.1)	1010 (39.8)	590 (23.2)	744 (29.3)	792 (31.2)	753 (29.7)
FLEX FUSION™ LIMITED 800mm WIDE X 1200mm DEEP	662 (26.1)	1160 (45.7)	590 (23.2)	894 (35.2)	942 (37.1)	753 (29.7)



2

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FRONT AND REAR E-RAIL POSITION RANGE

FRONT OF FRAME TO

FRONT RAIL

64mm (2.5")

64mm (2.5")

NOTE: MAXIMUM E-RAIL SPAN ONLY POSSIBLE IF NO PDU BRACKETS ARE INSTALLED

PART NO.	DESCRIPTION	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
XGL84212*	FLEXFUSION™ LIMITED CABINET	147 Kg/EACH	167 Kg/EACH
	800mm X 42RU X 1070mm DEEP W/SIDE PANELS	224 LBS/EACH	368 LBS/EACH
XGL84812*	FLEXFUSION™ LIMITED CABINET	163 Kg/EACH	181 Kg/EACH
	800mm X 48RU X 1070mm DEEP W/SIDE PANELS	359 LBS/EACH	399 LBS/EACH
XGL84222*	FLEXFUSION™ LIMITED CABINET	157 Kg/EACH	180 Kg/EACH
	800mm X 42RU X 1200mm DEEP W/SIDE PANELS	346 LBS/EACH	397 LBS/EACH
XGL84822*	FLEXFUSION™ LIMITED CABINET	174 Kg/EACH	195 Kg/EACH
	800mm X 48RU X 1200mm DEEP W/SIDE PANELS	384 LBS/EACH	430 LBS/EACH

* DENOTES COLOR "B" = BLACK "W" = WHITE

WIDTH

800

800

DEPTH

1070

1200

ABOVE WEIGHTS ARE CABINET THAT INCLUDES ALL PARTS SUPPLIED LISTED IN NOTE 8: FRAME, E-RAILS, TOP CAP, SIDE PANELS, SINGLE HINGED FRONT DOOR, SPLIT HINGED REAR DOOR, (1) SET OF PDU BRACKETS, (4) LEVELING LEGS, (4) CASTERS

FRONT TO REAR RAIL SPAN

166mm TO 915mm / (6.5" TO 36.0")

166mm TO 1065mm / (6.5" TO 42.0")

A								FLEXFUSION™ XGL 800mm CABINET FAMILY		
								CUSTOMER DRAWING		
								O1196EAW/00 DATASET FILE NAME 01196EAW DC/00A		
								01196EAW_DC/00A		
H								MATERIAL:	1	
ZE								N/A		
SI	00A	2/21/23	MEX- JAGC	TKW	ELE	DRAWING RELEASE	V09002UV/00	THIRD ANGLE PROJECTION DRAWING NUMBER: 01196EAW-DC		
NXGLOB,	REV	DATE	ВҮ	CHK	APR	DESCRIPTION	ECN	DRAWN BY MEX- JAGC 2/21/23 TKW NONE SHT 6 OF 6		
					ØI					

2

1