

The Safe and Secure Campus



When it comes to safety and security in school settings, most campuses today react to the reality that is ripped from the headlines. Security cameras keep an ever-present eye on not only buildings, but also parking lots and walkways.

Controlled access at doors limits those who can get inside buildings. Security staff monitor video surveillance to help prevent emergencies. Safety systems automatically alert local emergency services if an alarm sounds. It's all part of a global effort to keep students, faculty, and staff safe.

When safety and security are critical, you need a network infrastructure that ties it all together, and makes it easy to use and monitor. Panduit structured cabling solutions deliver reliable performance for these critical systems, including a full plenum offering for mounting and connecting security cameras in the ceiling; small diameter patch cords and high-density patching solutions help provide the space you need to connect backup systems and associated equipment in the telecommunications room.

∴ 93% of public schools control access to campus buildings; 75% use security cameras to monitor buildings and grounds
– National Center for Education Statistics

Part Number	Part Description
-------------	------------------

Horizontal Cables

PUP6AHD04BU-G	Category 6A U/UTP copper cable with Vari-MaTriX™ HD Technology, plenum, 4-pair, Blue.
PUFP6X04BU-UG	Category 6A U/FTP copper cable, plenum, 4-pair, Blue.
PUP6004BU-W	Category 6 U/UTP copper cable, plenum, 4-pair, Blue.
PUO6C04BL-U	Category 6 outside plant U/UTP copper cable with gel-filled construction to prevent moisture migration in underground or wet applications, 4-pair, Black.



Patch Cords

UTP28X3BU	Category 6A performance, 28 AWG, UTP patch cord, CM/LSZH, Blue, 3 ft.
STP28X10MBU	Category 6A performance, 28 AWG, F/UTP patch cord, CM/LSZH, Blue, 10m.
UTP28SP3BU	Category 6 performance, 28 AWG, UTP patch cord, CM/LSZH, Blue, 3 ft.



RJ45 Modules

FP6X88MTG	Category 6A UTP field term RJ45 plug for field termination of 4-pair unshielded twisted pair cable.
FPS6X88MTG	Category 6A shielded field term RJ45 plug for field termination of 4-pair shielded twisted pair cable.
CJ6X88TGBU	Category 6A, RJ45, 8-position, 8-wire UTP jack module with MaTriX Technology. Supports high-bandwidth applications and is ideal for running next generation Power over Ethernet (PoE++). UL Rated: UL 1863 and UL 2043.
CJS6X88TGY	Category 6A, RJ45, 8-position, 8-wire shielded jack module with MaTriX Technology. Supports high-bandwidth applications and is ideal for running next generation Power over Ethernet (PoE++). UL Rated: UL 1863 and UL 2043.
NK6X88MBU	Category 6A, 8-position, 8-wire keystone punchdown jack module.
CJ688TGBU	Category 6, RJ45, 8-position, 8-wire jack module. UL Rated: UL 1863 and UL 2043.
CJS688TGY	Category 6, RJ45, 8-position, 8-wire shielded jack module. UL Rated: UL 1863 and UL 2043.
NK688MBU	Category 6, 8-position, 8-wire keystone punchdown jack module.



Physical Security Products

SKRJ45RD-X	SmartKeeper RJ45 jack module blockout device; requires master key (SKMKEY) to unlock and remove.
SKUSBA-V	SmartKeeper USB Type A blockout device; requires master key (SKMKEY) to unlock and remove.
SKUSBC	SmartKeeper USB Type C blockout device; requires master key (SKMKEY) to unlock and remove.
SKMKEY	SmartKeeper master key for removal of all SmartKeeper blockout devices.



Accessories

CBX2IW-AY	Mini-Com® 2-port Surface Mount Box accepts up to two Mini-Com® Modules. UL Rated: UL 1863 and UL 2043; Off White.
NK2BXIW-A	NetKey® 2-port Surface Mount Box accepts up to two NetKey® Modules; Off White. Note: Not UL rated for use in plenum spaces.
JP2DW-L20	J-Pro™ Cable Support with clip for use with #12 wire and threaded rod; 2" bundle capacity; provides horizontal and vertical bend radius control to preserve cable performance and prevent damage; for use in plenum spaces; multiple colors and mounting options available.



See www.panduit.com for additional colors, sizes, cable jackets, and performance offerings.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com

or by phone: 800.777.3300

PANDUIT®

© 2021 Panduit Corp.
ALL RIGHTS RESERVED.
CPAG06--SA-ENG
2/2021