


Part



Cutout

NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [ ] ARE METRIC.
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
4. MATERIAL:  
ENCLOSURE: POLYAMIDE 6.6  
SEAL - NBR/EPDM
5. PROTECTION CLASS:  
NEMA 1,12  
IP 65
6. TEMPERATURE RANGE: -22 - 194 °F
7. RoHS COMPLIANT
8. COMPLIANCE: cURus (LOCKNUT IS NOT UL APPROVED)
9. FLAMMABILITY: HB
10. FOR SNAPPING INTO 0.06"-0.08" PLATES
11. SUPPLIED WITH LOCKNUT
12. WEIGHT: SEE TABLE

PART NUMBER	A	B	C	NUMBER OF OPENINGS		THREAD METRIC	D	PART WEIGHT	PKG QTY
	in. (mm)	in. (mm)	in. (mm)	TOTAL	NUMBER X DIA.		in. (mm)	lbs. (g)	
CESU2-RL504	2.28 (58)	0.35 (9)	0.94 (24)	4	3 x 0.24 - 0.39 (3 x 6 - 10)	M50x1.5	1.99 (50.5)	0.1 (45.5)	1
					1 x 0.38 - 0.63 (1 x 9.6 - 15.9)				
CESU2-RL506	2.28 (58)	0.35 (9)	0.94 (24)	6	1 x 0.12 - 0.22 (1 x 3 - 5.5)	M50x1.5	1.99 (50.5)	0.1 (45.5)	1
					5 x 0.20 - 0.36 (5 x 5 - 9.2)				
CESU2-RL508	2.28 (58)	0.35 (9)	0.94 (24)	8	7 x 0.14 - 0.26 (7 x 3.5 - 6.5)	M50x1.5	1.99 (50.5)	0.1 (45.5)	1
					1 x 0.24 - 0.39 (1 x 6 - 10)				
CESU2-RL5031	2.28 (58)	0.35 (9)	0.94 (24)	31	31 x 0.06 - 0.12 (31 x 1.5 - 3.1)	M50x1.5	1.99 (50.5)	0.1 (45.5)	1
CESU2-RL638	2.80 (71)	0.35 (9)	0.98 (25)	8	2 x 0.12 - 0.26 (2 x 3 - 6.5)	M63x1.5	2.50 (63.5)	0.149 (67.5)	1
					4 x 0.20 - 0.36 (4 x 5 - 9.2)				
					2 x 0.38 - 0.63 (2 x 9.6 - 15.9)				
CESU2-RL6313	2.80 (71)	0.35 (9)	0.98 (25)	13	6 x 0.12 - 0.22 (6 x 3 - 5.5)	M63x1.5	2.50 (63.5)	0.149 (67.5)	1
					6 x 0.14 - 0.26 (6 x 3.5 - 6.5)				
					1 x 0.24 - 0.39 (1 x 6 - 10)				
CESU2-RL6319	2.80 (71)	0.35 (9)	0.98 (25)	19	19 x 0.12 - 0.2 (19 x 3 - 5)	M63x1.5	2.50 (63.5)	0.149 (67.5)	1
CESU2-RL6346	2.80 (71)	0.35 (9)	0.98 (25)	46	46 x 0.06 - 0.12 (46 x 1.5 - 3.1)	M63x1.5	2.50 (63.5)	0.149 (67.5)	1



PART NUMBER		SEE TABLE	
TITLE		CESU2-RL Control Drawing	
CUSTOMER DRAWING			
ITEM REVISION NAME	00872EBF/00	<b>PANDUIT</b>	
DATASET FILE NAME	00872EBF_DC/00A		
THIRD ANGLE PROJECTION		DRAWING NUMBER	
MATERIAL		SEE NOTE 4	00872EBF - DC
DRAWN BY	DATE	CHK	SCALE
SERH	9/13/2022	SERH	1:1
SHEET 1 OF 1		B	

00A	9/13/2022	SERH	MDS	JADE	INITIAL RELEASE	124032/00
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

B-SIZE CUSTOMER