THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
JFPAOSP6TG**	.28 LB/10 PCS (127 g/10 PCS)



NOTES:
1. SEE PANDUT WEBSITE FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE PANDUIT WEBSITE FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
   1- ADAPTER WITH OPAQUE DOOR AND LAN/CAT6 PRINT
   1- MINI-COM CAT6 JACK MODULE





VIEW SHOWN WITH A STANDARD TERMINATION CAP.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	6-28-17	BJN	MIBA	MMR	RELEASED TO PRODUCTION	02079CC-01

TITLE

MINI-COM 1 POSITION JIS SHUTTERED ADAPTER KIT

CUSTOMER DRAWING

ITEM REVISION NAME: M02079CC/00

DATASET FILE NAME: M02079CC_DC01/00A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .1 [2.54] .XXX ± .005 [.127]
.XX ± .01 [.25] ANGLES ± 5 °
THIRD ANGLE PROJECTION

MATERIAL:
ADAPTER- ABS
DOOR- ABS

DRAWING NUMBER: 02079CC-01

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
BJN	6-28-17	MIBA	NONE		A

D10100DA/14